



# MASTERColour CDM-T

## MASTERColour CDM-T 35W/842 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information	
Cap base	G12 [ G12]
Operating position	UNIVERSAL [ Any or Universal (U)]
Life to 5% failures (nom.)	9000 h
Life to 10% failures (nom.)	10000 h
Life to 20% failures (nom.)	11000 h
Life to 50% failures (nom.)	12000 h
ANSI code HID	-
Light technical	
Colour Code	842 [ CCT of 4.200 K]
Luminous flux (rated) (nom.)	3000 lm
Colour designation	Cool White (CW)

Lumen maintenance 10,000 hours (nom.)	70 %
Lumen maintenance 2,000 hours (min.)	80 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (min.)	75 %
Lumen maintenance 5,000 hours (nom.)	85 %
Chromaticity coordinate X (nom.)	0.370
Chromaticity coordinate Y (nom.)	0.367
Correlated Colour Temperature (Nom)	4200 K
Luminous efficacy (rated) (nom.)	77 lm/W
Colour rendering index (nom.)	84

Operating and electrical	
Power (Rated) (Nom)	39.1 W

## MASTERColour CDM-T

Lamp current run-up (max.)	0.720 A
Ignition supply voltage (max.)	198 V
Ignition peak voltage (max.)	5000 V
Ignition supply voltage (min.)	198 V
Ignition peak voltage (min.)	3500 V
Re-ignition time (min.) (max.)	15 min
Ignition time (max.)	30 s
Voltage (Max)	93 V
Voltage (Min)	77 V
Voltage (Nom)	85 V

### Controls and dimming

Dimmable	No
Run-up time 90% (max.)	3 min

### Mechanical and housing

Lamp Finish	Clear
Bulb shape	T19 [ T 19mm]

### Approval and application

Mercury (Hg) content (nom.)	2.7 mg
Energy consumption kWh/1,000 hours	43 kWh

### UV

PET (NIOSH) (min.)	8 h/500lx
--------------------	-----------

Damage factor D/fc (max.)	0.5
---------------------------	-----


### Luminaire design requirements

Bulb temperature (max.)	500 °C
Cap-base temperature (max.)	280 °C
Cap-Base Temperature (Max)-DUP(do not use)	536 °F
Pinch temperature (max.)	350 °C
Pinch Temperature (Max)-DUP(do not use)	350 °C

### Product data

Full product code	871869648445600
Order product name	MASTERColour CDM-T 35W/842 G12 1CT/12
EAN/UPC – product	8718696484456
Order code	48445600
SAP numerator – quantity per pack	1
Local code description	LAMPADA HALETO METALICO CDM-T35W/842G12
Numerator – packs per outer box	12
SAP material	928094305129
Net Weight (Piece)	28.000 g
ILCOS code	MT/UB-35/842-H-G12-20/90

## Dimensional drawing




MASTERColour CDM-T 35W/842 G12 1CT/12

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERColour CDM-T 35W/842 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm








# MASTERCoulour CDM-T

## Photometric data



LDLD\_CDM-T\_0001-Light distribution diagram

LDLD\_CDM-T\_0002-Light distribution diagram




LDLD\_CDM-T\_0005-Light distribution diagram

LDPO\_CDM-T\_35W\_842-Spectral power distribution Colour

# MASTERCcolour CDM-T

## Lifetime



LDLE\_CDM-T\_0001-Life expectancy diagram

