

# Ecofit Ledtubes T8

## LEDtube 600mm 8W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data


General Information		Power factor (nom.)		0.5
Cap base	G13 [ Medium Bi-Pin Fluorescent]	Voltage (Nom)	220–240 V	
EU RoHS compliant	Yes	<b>Temperature</b>		
Nominal lifetime (nom.)	15000 h	T-ambient (max.)	45 °C	
Switching cycle	50,000X	T-ambient (min.)	-20 °C	
<b>Light Technical</b>		T storage (max.)	65 °C	
Colour Code	740 [ CCT of 4,000 K]	T storage (min.)	-40 °C	
Beam Angle (Nom)	240 °	T-Case maximum (nom.)	60 °C	
Luminous flux (nom.)	800 lm	<b>Controls and Dimming</b>		
Colour designation	Cool White (CW)	Dimmable	No	
Correlated Colour Temperature (Nom)	4000 K	<b>Mechanical and Housing</b>		
Luminous efficacy (rated) (nom.)	100.00 lm/W	Product length	600 mm	
Colour consistency	<7	<b>Approval and Application</b>		
Colour rendering index (nom.)	73	Energy efficiency label (EEL)	A+	
LLMF at end of nominal lifetime (nom.)	70 %	Energy-saving product	Yes	
<b>Operating and Electrical</b>		Suitable for accent lighting	No	
Input frequency	50 to 60 Hz	Approval marks	RoHS compliance KEMA Keur certificate	
Power (Rated) (Nom)	8 W			
Starting time (nom.)	0.5 s			
Warm-up time to 60% light (nom.)	0.5 s			

# Ecofit Ledtubes T8

Energy consumption kWh/1,000 hours	8 kWh
<b>Product Data</b>	
Full product code	871869652505000
Order product name	LEDtube 600mm 8W 740 T8 AP C G
EAN/UPC – product	8718696525050
Order code	52505000

SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001184708
SAP net weight (piece)	0.124 kg



## Dimensional drawing



**TLED 600mm 2ft T8 8W-18W 4000K G13 ND**


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP C	mm	mm	mm	mm	mm	mm	mm
G							

## Photometric data



**LEDtube 600mm 8W 740 T8 CN I G**



**LEDtube 600mm 8W 765 T8 CN I G**



**LEDtube 600mm 8W G13 T8 740 800lm AP C G**



# Ecofit Ledtubes T8

## Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

## Ecofit Ledtubes T8

