



# CorePro LED PLC 2P

## LED PLC 6.5W 830 2P G24d-2

The CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings and is environmentally friendly.

### Product data

General Information		Warm-up time to 60% light (nom.)	
Cap base	G24D-2 [ G24d-2]		0.5 s
EU RoHS compliant	Yes	Power factor (nom.)	0.9
Nominal lifetime (nom.)	30000 h	Voltage (Nom)	220-240 V
Switching cycle	50,000X	<b>Temperature</b>	
<b>Light Technical</b>		T-ambient (max.)	35 °C
Colour Code	830 [ CCT of 3,000 K]	T-ambient (min.)	-20 °C
Beam Angle (Nom)	120 °	T storage (max.)	65 °C
Luminous flux (nom.)	650 lm	T storage (min.)	-40 °C
Colour designation	White (WH)	T-Case maximum (nom.)	65 °C
Correlated Colour Temperature (Nom)	3000 K	<b>Controls and Dimming</b>	
Luminous efficacy (rated) (nom.)	100.00 lm/W	Dimmable	No
Colour consistency	<6	<b>Mechanical and Housing</b>	
Colour rendering index (nom.)	83	Product length	100 mm
LLMF at end of nominal lifetime (nom.)	70 %	Bulb shape	Tube, single-ended
<b>Operating and Electrical</b>		<b>Approval and Application</b>	
Input frequency	50 to 60 Hz	Energy-saving product	Yes
Power (Rated) (Nom)	6.5 W	Approval marks	TUV CE marking RoHS compliance KEMA Keur certificate
Lamp current (max.)	35 mA		
Lamp current (min.)	25 mA		
Starting time (nom.)	0.5 s		

# CorePro LED PLC 2P

Energy consumption kWh/1,000 hours 9 kWh

## Product Data

Full product code	871869667003300
Order product name	LED PLC 6.5W 830 2P G24d-2
EAN/UPC – product	8718696670033
Order code	67003300

SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001201408
SAP net weight (piece)	0.080 kg


## Dimensional drawing




Product	D1	D2	A1	A2	A3
LED PLC 6.5W 830 2P G24d-2	24.3 mm	28.4 mm	105.8 mm	125 mm	147.6 mm

## LED PLC 6.5W 830 2P G24d-2


## Photometric data



General Uniform Lighting  
PLC 6.5W 830 2P G24d-2  
Page 10





## LEDtube PLC 100mm 7W G24D-2 830 650lm





# CorePro LED PLC 2P

## Lifetime




LEDtube PLC 100mm 7W G24D-2 830 650lm

LEDtube PLC 100mm 7W G24D-2 830 650lm



LEDtube PLC 100mm 7W G24D-2 830 650lm

LEDtube PLC 100mm 7W G24D-2 830 650lm



LEDtube PLC 100mm 7W G24D-2 830 650lm

## CorePro LED PLC 2P

