

# Classic filament LEDbulbs

## LEDClassic 4-50W A60 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
Technical type	4-50W
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	118.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	33 mA
Wattage equivalent	50 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [ A 60mm]
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	4 kWh
Product Data	
Full product code	871869657419500

# Classic filament LEDbulbs

Order product name	LEDClassic 4-50W A60 E27 WW CL ND APR
EAN/UPC – product	8718696574195
Order code	57419500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12

SAP material	929001237108
SAP net weight (piece)	0.030 kg



## Dimensional drawing

... D ...

Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm


filament 4.5W-40W 470lm NAD 2700K E27ND

## Photometric data



LED Lamps, Lightcolour /827 ND CL

CorePro LEDbulb ND 4-40W A60 827



CorePro LEDbulb ND 4-40W A60 827

## Classic filament LEDbulbs

