



Classic filament LEDbulbs

LEDClassic 4-50W ST64 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Starting time (nom.)	
Cap base	E27 [E27]		0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.4
Switching cycle	20,000X	Voltage (Nom)	220-240 V
Technical type	4-50W		
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	70 °C
Luminous flux (nom.)	470 lm		
Colour designation	Warm White (WW)	Controls and Dimming	
Correlated Colour Temperature (Nom)	2700 K	Dimmable	No
Luminous efficacy (rated) (nom.)	118.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (nom.)	80	Bulb shape	ST64
LLMF at end of nominal lifetime (nom.)	70 %	Approval and Application	
Operating and Electrical		Energy-saving product	Yes
Input frequency	50 to 60 Hz	Suitable for accent lighting	No
Power (Rated) (Nom)	4 W	Energy consumption kWh/1,000 hours	4 kWh
Lamp current (nom.)	33 mA	Product Data	
Wattage equivalent	50 W	Full product code	871869657423200

Classic filament LEDbulbs

Order product name	LEDClassic 4-50W ST64 E27 WW CL ND APR
EAN/UPC – product	8718696574232
Order code	57423200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6

SAP material	929001237308
SAP net weight (piece)	0.048 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
LEDClassic 4-50W ST64 E27 WW CL ND APR	64 mm	140 mm


Photometric data



LED Lamps, Lightcolour /827 ND CL




CorePro LEDbulb ND 4-40W ST64 827



CorePro LEDbulb ND 4-40W ST64 827

Classic filament LEDbulbs

Lifetime



15K LED

15K LMP

