



# CorePro LED PLC 2P

## LED PLC 8.5W 865 2P G24d-3

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

### Product data

General Information	
Cap-Base	G24D-3 [G24d-3]
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,000 lumen
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	117.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8.5 W
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	200 mm
Bulb Shape	Tube, single-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	11 kWh
Product Data	
Full product code	871869666995200

# CorePro LED PLC 2P

Order product name	LED PLC 8.5W 865 2P G24d-3
Order code	66995200
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001280108


Full product name	LED PLC 8.5W 865 2P G24d-3
EAN/UPC - Case	8718696669969

## Dimensional drawing




Product	D1	D2	A1	A2	A3
LED PLC 8.5W 865 2P G24d-3	24.3 mm	28.4 mm	128.8 mm	148 mm	170.6 mm

## Photometric data




General Information E1 Photo Lighting E1 Page 117



General uniform lighting - LED PLC 8.5W 865 2P G24d-3



Spectral Power Distribution Colour - LED PLC 8.5W 865 2P G24d-3



Light Distribution Diagram - LED PLC 8.5W 865 2P G24d-3

# CorePro LED PLC 2P


## Lifetime




Life Expectancy Diagram - LED PLC 8.5W 865 2P G24d-3



Life Expectancy Diagram - LED PLC 8.5W 865 2P G24d-3



Life Expectancy Diagram - LED PLC 8.5W 865 2P G24d-3



Lumen Maintenance Diagram - LED PLC 8.5W 865 2P G24d-3

Lumen Maintenance Diagram - LED PLC 8.5W 865 2P G24d-3

## CorePro LED PLC 2P

