



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 20W 15D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General information		Lamp current (nom.)	
Cap base	E27 [ E27]		95 mA
EU RoHS compliant	Yes	Wattage equivalent	35 W
Nominal lifetime (nom.)	25000 h	Starting time (nom.)	0.5 s
Switching cycle	50000	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.9
		Voltage (Nom)	220-240 V
Light technical		Temperature	
Colour Code	841 [ CCT of 4100K (841)]	T-Case maximum (nom.)	67 °C
Beam Angle (Nom)	15 °		
Luminous flux (nom.)	1850 lm	Controls and dimming	
Colour designation	Cool White (CW)	Dimmable	No
Correlated Colour Temperature (Nom)	4000 K		
Luminous efficacy (rated) (nom.)	92.00 lm/W	Mechanical and housing	
Colour consistency	<6	Bulb shape	PAR30L [ PAR 3.75 inch/95mm Long]
Colour rendering index (nom.)	82		
LLMF at end of nominal lifetime (nom.)	70 %	Approval and application	
		Suitable for accent lighting	Yes
		Energy consumption kWh/1,000 hours	20 kWh
Operating and electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	20 W		


# MASTER LEDspot PAR High Lumen

## Product data

Full product code	871869673129100
Order product name	Master LED PAR30L 20W 15D 840
EAN/UPC – product	8718696731291
Order code	73129100
SAP numerator – quantity per pack	1

Numerator – packs per outer box	6
SAP material	929001353908
Net Weight (Piece)	0.410 kg


## Dimensional drawing




Master LED PAR30L 20W 15D 840

Product	D	C
Master LED PAR30L 20W 15D 840	95.5 mm	129 mm


## Photometric data



LEDspot PAR30L E27 20W 4000K 15D



LEDspot PAR30L E27 20W 4000K 15D



LEDspot PAR30L E27 20W 4000K 15D

# MASTER LEDspot PAR High Lumen

## Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

