



MASTER LEDspot PAR High Lumen

Master LED PAR30L 40W 30D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data

General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	40-70W
Light Technical	
Colour Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	30 °
Luminous flux (nom.)	4600 lm
Luminous intensity (nom.)	14000 cd
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	40 W
Lamp current (nom.)	196 mA
Wattage equivalent	70 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	PAR30L [PAR 3.75 inch/95mm Long]

MASTER LEDspot PAR High Lumen

Approval and Application


Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	40 kWh

Product Data

Full product code	871869675945500
Order product name	Master LED PAR30L 40W 30D 840
EAN/UPC – product	8718696759455

Order code	75945500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	929001374908
SAP net weight (piece)	0.410 kg


Dimensional drawing




Master LED PAR30L 40W 30D 840

Product	D	C
Master LED PAR30L 40W 30D 840	95.5 mm	129 mm

Photometric data





LEDspot E27 PAR30L 40W 4000K



LEDspot E27 PAR30L 40W 4000K

MASTER LEDspot PAR High Lumen

Lifetime



LEDspot E27 PAR30L 35W 4000K

LEDspot E27 PAR30L 35W 4000K

