



Digital ignitors for maximum reliability

Electronic series ignitor for HID lamp circuits

HID ignitors for series systems

Benefits

- Easy installation and wiring
- Can operate with both semi-parallel and series ballasts
- Digital ignitors ensure maximum reliability

Features

- Ignitors equipped with screw terminal blocks as standard
- Series ignitor will only work in series circuits

Application

- Outdoor lighting (most popular application: roads and tunnels)

Versions



SU 50 & 52

Electronic series ignitor for HID lamp circuits

Dimensional drawing

| Product | C1 | A1 | A2 | B1 | D1 |
|---------|-------|-------|-------|-------|--------|
| SU 52 | 50 mm | 90 mm | 69 mm | 55 mm | 4.3 mm |

