



A reliable solution for essential projects.

CoreLine Value Highbay

CoreLine Value High-bay is the right choice for projects where essential specification and ease of installation are key. It comes with a trusted, high light quality, good service lifetime, energy savings and less maintenance. CoreLine Value High-bay delivers clear benefits for the installer too. The luminaire can be installed on the existing grid, and electrical connection is straightforward – there is no need to open the luminaire for installation and the external IP65 connector makes things easy to handle. A selection of optional accessories are available, including reflectors and a bracket to further increase installation flexibility.

Benefits

- Fulfils needs of essential projects, thanks to robust design and high water and dust-proof rating (IP65)
- Saves on energy and maintenance costs
- Easy installation thanks to single suspension hook and external connector

Features

- Modern, high-quality die-cast aluminium housing
- Long lifetime and high efficiency: 50.000 hours with flux at 70% min. compared to initial level
- High efficiency: up to 140lm/W
- IP65 external electrical connection
- Selection of optional accessories: reflectors and mounting bracket

Application

- General manufacturing
- Warehouses and logistical centres



CoreLine Value Highbay

Versions



CoreLine High-bay Value BY101P

Dimensional drawing



Product details

CoreLine High-bay Value BY101P
connector DPP4



CoreLine High-bay Value BY101P
with hook 2 DPP3



CoreLine High-bay Value BY101P
front DPP5

