



# CoreLine Trunking Gen2

## LL212X 80S/840 1x PSU NB 5x2.5 HE

LL212X | Coreline Trunking Gen2 - Power supply unit - Narrow beam - 35° x 71°

CoreLine Trunking Gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking Gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

### Product data

General Information		Light source color	
Light source replaceable	No		840 neutral white
Number of gear units	1 unit	Optic type	Narrow beam
Driver included	Yes	Luminaire light beam spread	35° x 71°
Service tag	Yes	Unified glare rating CEN	22
Product family code	LL212X [Coreline Trunking Gen2]	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220 to 240 V
Value ladder	Value	Line Frequency	50 to 60 Hz
		Input Frequency	50 to 60 Hz
		Initial CLO power consumption	- W
		Average CLO power consumption	- W
		Power Consumption	49 W
		Inrush current	22.5 A
		Inrush time	0.225 ms
		Power Factor (Fraction)	0.95

## CoreLine Trunking Gen2

Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	23

### Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (ON/OFF)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Color	White RAL9016
Optical cover/lens finish	Frosted
Overall length	1,130 mm
Overall width	80 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 80 x 1130 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC plus mark

Warranty period	5 years
EU RoHS compliant	Yes

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

### Application Conditions


Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

### Product Data

Full product code	871951463818100
Order product name	LL212X 80S/840 1x PSU NB 5x2.5 HE
Order code	63818100
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material number (12NC)	910925868840
Full product name	LL212X 80S/840 1x PSU NB 5x2.5 HE
EAN/UPC - Case	8719514638181



## Dimensional drawing



## CoreLine Trunking Gen2

