



UniDot G2

BGS302 G2 9LED 30K 24V DSC

724 lm - 9 W - 3000 K

UniDot G2 is a surface-mounted, exterior-rated and compact-sized architectural LED direct-view dot lighting luminaire that is designed for façade and outdoor lighting applications. The robust mechanical and unique optical covers make UniDot G2 ideal for building facades, bridges, theatres, amusement parks and recreational centres. Available in white, monochromatic colours, RGB, RGBW and tunable white. Three optical cover options and a DMX control interface is available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Product data

General Information		
Light source colour	Warm white	units, surge-protection device, front cover and mechanical parts
Light source replaceable	No	
Driver/power unit/transformer	PSU-E [Power supply unit external (PSU)]	
Driver included	No	
Optical cover/lens type	Polycarbonate bowl/cover spherical	
Control interface	-	
Connection	2 push-in connectors 2-pole	
Cable	2 cables 0.3 m with connector 2-pole	
Protection class IEC	Safety class III (III)	
Flammability mark	F [For mounting on normally flammable surfaces]	
CE mark	CE mark	
Light source engine type	LED	
Serviceability class	Class B, the luminaire is equipped with some serviceable parts (when applicable): driver, control	
Light Technical		
Standard tilt angle post-top	-	
Standard tilt angle side entry	-	
Operating and Electrical		
Input Voltage	24 DC V	
Input frequency	- Hz	
Power factor (min.)	0.9	
Controls and Dimming		
Dimmable	No	
Mechanical and Housing		
Housing material	Aluminum die-cast	

UniDot G2

Optical cover/lens material	Polycarbonate
Mounting device	No [-]
Optical cover/lens shape	Hemispherical
Overall length	136 mm
Overall width	124 mm
Overall height	83 mm
Overall diameter	124 mm
Colour	Dark gray

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	724 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	80 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	80

Initial chromaticity	4 SDCM
Initial input power	9 W
Power consumption tolerance	+/-10%

Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	911401752782
Order product name	BGS302 G2 9LED 30K 24V DSC
Order code	01752782
SAP numerator – quantity per pack	1
Numerator – packs per outer box	18
SAP material	911401752782
SAP net weight (piece)	0.388 kg



Dimensional drawing



BGS302 G2 9LED 30K 24V DSC

