



CoreLine Recessed Spot gen2

RS150Z CFRM RND-ADJUST D80 WH

- White

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

| General Information | | Input Frequency | |
|--------------------------|-------------|------------------------|----------|
| Angle | 20° | - Hz | |
| Accessory color | White | Mechanical and Housing | |
| Value ladder | Performance | Overall height | 29 mm |
| | | Overall diameter | 95 mm |
| Operating and Electrical | | Material | Aluminum |
| Input Voltage | - V | | |
| Line Frequency | - Hz | | |

CoreLine Recessed Spot gen2

Approval and Application

| | |
|------------------------------|--------------|
| Ingress protection code | - |
| Mech. impact protection code | IK03 [0.3 J] |
| Protection class IEC | - |

Product Data

| | |
|--------------------|-------------------------------|
| Full product code | 871951493847299 |
| Order product name | RS150Z CFRM RND-ADJUST D80 WH |
| Order code | 93847299 |

| | |
|---------------------------------|-------------------------------|
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 18 |
| Material number (12NC) | 911401811684 |
| Full product name | RS150Z CFRM RND-ADJUST D80 WH |
| EAN/UPC - Case | 8719514938588 |

