



CoreLine Recessed Spot gen2

RS150Z CFRM SQR-ADJUST D80 ALU

- Aluminum

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

General Information		Input Frequency	
Angle	20°		- Hz
Accessory color	Aluminum	Mechanical and Housing	
Value ladder	Performance	Overall length	95 mm
		Overall width	95 mm
		Overall height	29 mm
Operating and Electrical		Dimensions (Height x Width x Depth)	29 x 95 x 95 mm
Input Voltage	- V		
Line Frequency	- Hz		

CoreLine Recessed Spot gen2

Material	Aluminum
----------	----------

Approval and Application

Ingress protection code	-
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	-

Product Data

Full product code	871951493851999
Order product name	RS150Z CFRM SQR-ADJUST D80 ALU

Order code	93851999
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material number (12NC)	911401812084
Full product name	RS150Z CFRM SQR-ADJUST D80 ALU
EAN/UPC - Case	8719514938625

