



# CoreLine Recessed Spot gen2

RS150Z CFRM RND-ADJUST D80 WH HALOX100

- White

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

### Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

### Product data

General Information		Input Frequency	
Angle	20°		- Hz
Accessory color	White	Mechanical and Housing	
Value ladder	Performance	Overall height	29 mm
		Overall diameter	95 mm
		Material	Aluminum
Operating and Electrical			
Input Voltage	- V		
Line Frequency	- Hz		

## CoreLine Recessed Spot gen2

### Approval and Application

Ingress protection code	-
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	-

### Product Data

Full product code	871951493853399
Order product name	RS150Z CFRM RND-ADJUST D80 WH HALOX100
Order code	93853399

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material number (12NC)	911401812284
Full product name	RS150Z CFRM RND-ADJUST D80 WH HALOX100
EAN/UPC - Case	8719514938649

