



# CoreLine Recessed Spot gen2

## RS155Z MODULE LED6-WB-/840 D68 PSR

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

### Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

### Product data

General Information		Color rendering index (CRI)	
Light source replaceable	Yes	Color rendering index (CRI)	>80
Number of gear units	1 unit	Flickering value (PstLM)	1
Driver included	Yes	Stroboscopic effect value (SVM)	0.4
Value ladder	Performance	Beam angle of light source	120 degree(s)
Light Technical		Light source color	840 neutral white
Luminous Flux	800 lumen	Optic type	Beam angle 36°
Saturated Red (R9)	<50	Luminaire light beam spread	36°
Correlated Color Temperature (Nom)	4000 K	Unified glare rating CEN	30
Luminous Efficacy (rated) (Nom)	110 lm/W	Operating and Electrical	
		Input Voltage	220 to 240 V

## CoreLine Recessed Spot gen2

Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Power Consumption	7.2 W
Inrush current	2 A
Inrush time	0.02 ms
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	Cable 0.25 m with connector 3-pole
Number of products on MCB of 16 A type B	40

### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (ON/OFF)
Control interface	depends on driver (1-10V, DALI...)
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Color	Black
Optical cover/lens finish	Textured
Overall height	62 mm
Overall diameter	58 mm

### Approval and Application

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Warranty period	5 years

Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life	5 %
50000 h	
Lumen maintenance at median useful life*	-
35000 h	
Lumen maintenance at median useful life*	70
50000 h	
Lumen maintenance at median useful life*	-
75000 h	
Lumen maintenance at median useful life*	-
100000 h	

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10% (depends on dimmer, ELV)
Suitable for random switching	No

### Product Data

Full product code	871951494108399
Order product name	RS155Z MODULE LED6-WB-/840 D68 PSR
Order code	94108399
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material number (12NC)	911401823484
Full product name	RS155Z MODULE LED6-WB-/840 D68 PSR
EAN/UPC - Case	8719514941472



# CoreLine Recessed Spot gen2

## Dimensional drawing

