



CoreLine Recessed Spot gen2

RS155Z CFRM RND-ADJUST D70 ALU

- Aluminum

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

General Information		Input Frequency	
Angle	20°	- Hz	
Accessory color	Aluminum	Mechanical and Housing	
Value ladder	Performance	Overall height	29 mm
		Overall diameter	85 mm
		Material	Aluminum
Operating and Electrical			
Input Voltage	- V		
Line Frequency	- Hz		

CoreLine Recessed Spot gen2

Approval and Application

Ingress protection code	-
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	-

Product Data

Full product code	871951494115199
Order product name	RS155Z CFRM RND-ADJUST D70 ALU
Order code	94115199

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18
Material number (12NC)	911401824184
Full product name	RS155Z CFRM RND-ADJUST D70 ALU
EAN/UPC - Case	8719514941540



Dimensional drawing

