

# HID-High Power ballasts for SON/MH lamps

## BSN 1000 L 302 I

Impregnated (HID standard) electromagnetic ballasts, of copper/iron construction, for use in combination with an external ignitor, for HID lamps


### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Full product code	697480505005500

Order product name	BSN 1000L 302I
Order code	05005500
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710106742
Full product name	BSN 1000 L 302 I
EAN/UPC - Case	6974805050062
EAN/UPC - Product/Case	6974805050055

## HID-High Power ballasts for SON/MH lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 1000L 302I	7 mm	102.0 mm	183 mm	134.5 mm	117.0 mm

