



Xitanium LED linear drivers – non-isolated

Xitanium 35W 0.08-0.35A 150V S 230V

Xitanium linear non-isolated drivers are ideal for high voltage (HV) professional general lighting applications. The range includes DALI dimmable and programmable, 1-10V dimmable, non-dimmable and single current versions. They offer high efficiency, good quality of light and full flexibility. The new generation of 16mm DALI drivers offer ultimate performance. They comply with the latest DiiA standards, including implementation of the new DALI parts related to data. Configuring the drivers can be done quickly and wirelessly with SimpleSet. The new 21mm DALI drivers offer the best value for money.

Product data

General Information	
Lighting Technology	LED
Operating and Electrical	
Output Current (Max)	350 mA
Output Power (Max)	35 W
Output Power (Min)	10 W
Output Current (Min)	80 mA
Output Voltage (Max)	150 V
Output Voltage (Min)	50 V
Mechanical and Housing	
Housing	Office 280x30x21 4p2p NFC

Product Data	
Full product code	871869655585900
Order product name	Xitanium 35W 0.08-0.35A 150V S 230V
Order code	55585900
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	929001506406
Full product name	Xitanium 35W 0.08-0.35A 150V S 230V
EAN/UPC - Case	8718696555866