

# PHILIPS

# Lighting



## Xitanium LED linear drivers – non-isolated

### Xitanium 60W 0.15–0.5A 220V TD21 230V

Xitanium linear non-isolated drivers are ideal for high voltage (HV) professional general lighting applications. The range includes DALI dimmable and programmable, 1–10V dimmable, non-dimmable and single current versions. They offer high efficiency, good quality of light and full flexibility. The new generation of 16mm DALI drivers offer ultimate performance. They comply with the latest DiiA standards, including implementation of the new DALI parts related to data. Configuring the drivers can be done quickly and wirelessly with SimpleSet. The new 21mm DALI drivers offer the best value for money.

#### Product data

General Information	
Nominal lifetime	100,000 hour(s)
Lighting Technology	LED
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Mains voltage operation (DC)	168–275 V
Total Harmonic Distortion IEC (Max)	20 %
Output Current Ripple (Max)	4 %
Maximum Efficiency at Full Load	91.2 %
Output Current (Max)	500 mA
Output Current Tolerance (Max)	5 %
Mains voltage performance (DC)	186–250 V
Power Factor (Fraction)	0.9
Open Circuit Voltage (DC) (Max)	250 V
Protection Level Up (L–N) at 5 kA (Max)	1 kV
Protection Level Up (LN–Earth) at 5 kA (Max)	2 kV
Input current (AC)	0.3 mA
Input current (DC)	0.35
Inrush Current Peak (Max)	25.1 A
Output Power (Max)	60 W
Default output current	150 mA
Inrush Current Width to 50% of Peak	214 μs
Power Factor 100% Load (Max)	0.9
Energy Metering	No
Constant Current (CC)	True
Constant Voltage (CV)	False
Diagnostics	True
Output Power (Min)	17 W
Output Current (Min)	150 mA
Output Voltage (Max)	220 V
Output Voltage (Min)	50 V

## Xitanium LED linear drivers – non-isolated

Number of Products on MCB (16A Type-C) (Max)	21 piece/unit
<b>Wiring</b>	
Connector Type Input Terminals	Wago 744
Hot Wiring	no
Connector Type Output Terminals	Wago 744
Output Wire Cross Section (Max)	1.5 mm <sup>2</sup>
Output Wire Cross Section (Min)	0.5 mm <sup>2</sup>
Cable Length From Device to Lamp	2 m
Input Wire Gauge	16-20
Input wire strip length	8 mm to 9 mm mm
Input Wire Cross Section (Max)	1.5 mm <sup>2</sup>
Input Wire Cross Section (Min)	0.5 mm <sup>2</sup>
Output wire strip length	8 mm to 9 mm mm
<b>System characteristics</b>	
Central DC Operation	Yes
YellowDot ready	No
<b>Temperature</b>	
Ambient temperature range	-25 °C to 50 °C
T-Case Lifetime (Max)	65 °C
T-Case Maximum (Max)	75 °C
Module Temperature Protection	no
Maximum case temperature (in case of failure)	110 °C
<b>Controls and Dimming</b>	
Dimmable	DALI
Dimming Range	100-1%
D4i compliant	No
DynaDimmer	No
Constant light output	Programmable

<b>Mechanical and Housing</b>	
Product Length	280 mm
Housing	Office 280x30x21 7p4p
Overall length	280 mm
Overall width	30 mm
Overall height	21 mm
Dimensions (Height x Width x Depth)	21 x 30 x 280 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Isolation Classification	No
Short Circuit Protection	Protected
Over Power Protection	Protected
Open Circuit Protection	Protected
Approval Marks	CCC certificate CE marking ENEC certificate RCM compliance REACH compliance RoHS compliance
Corridor Mode	True
Output Current Set Options	LEDset, Programmable
Protection class IEC	Safety class I
<b>Product Data</b>	
Full product code	871869965377400
Order product name	XITANIUM 60W 0.15-0.5A 220V TD21 230V
Order code	65377400
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	929001681906
Full product name	Xitanium 60W 0.15-0.5A 220V TD21 230V
EAN/UPC - Case	8718699653781

