



Widest product range in the world!

MASTER PL-T 2 Pin

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Substantially more light (about 15% more) per light point than with other similar shapes
- Multiple light color choice
- Good color rendering (CRI >80)

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Philips' bridging technology applied
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life
- Fast light run-up

Application


- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units

MASTER PL-T 2 Pin


Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/840/2P 1CT/ 5X10BOX	41 mm	71.8 mm	96.0 mm	119.2 mm



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 26W/830/2P 1CT/ 5X10BOX	41 mm	86.7 mm	111.0 mm	134.2 mm
MASTER PL-T 26W/840/2P 1CT/ 5X10BOX	41 mm	86.7 mm	111.0 mm	134.2 mm

MASTER PL-T 2 Pin

Approval and Application

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg

Controls and Dimming

Dimmable	No
----------	----

General Information

Life To 10% Failures (Nom)	6500 h
Life To 50% Failures (Nom)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %

Light Technical

LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	81 %

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	22 kWh
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	32 kWh
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	32 kWh

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	0.225 A	18 W
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	0.335 A	26.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	0.335 A	26.0 W

General Information

Order Code	Full Product Name	Cap-Base
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	GX24D-2
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	GX24D-3

Order Code	Full Product Name	Cap-Base
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	GX24D-3

Light Technical (1/2)

Order Code	Full Product Name	Colour Code	Colour Designation	Correlated	
				Colour Temperature (Nom)	Colour Rendering Index (Nom)
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	841	Cool White (CW)	4000 K	82
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	830	Warm White (WW)	3000 K	>80

Order Code	Full Product Name	Colour Code	Colour Designation	Correlated	
				Colour Temperature (Nom)	Colour Rendering Index (Nom)
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	841	Cool White (CW)	4000 K	82

Light Technical (2/2)

MASTER PL-T 2 Pin

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
61061470	MASTER PL-T 18W/ 840/2P 1CT/5X10CC	67 lm/W	1200 lm	1200 lm
61102470	MASTER PL-T 26W/ 830/2P 1CT/5X10CC	66 lm/W	1800 lm	1725 lm

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
61113070	MASTER PL-T 26W/ 840/2P 1CT/5X10CC	66 lm/W	1800 lm	1725 lm

