



Spot of crisp white light

Accentline

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours


Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Dichroic coating
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

Dimensional drawing



Product	D (max)	C (max)
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

