



MSR Gold™ SA Double Ended – for extended performance

MSR Gold™ SA Double Ended

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Pure, white light; color point close to black body line. Consistent color impression over MSR Range
- Reduces early lamp or lamp holder failures

Features

- Philips Pinch Protection
- MSR filling
- Gold plated lamp caps

Application

- Entertainment

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MSR Gold™ SA Double Ended

Versions



Dimensional drawing



Product	D (max)	O	A	C (max)		
MSR Gold™ 1510 SA/DE UNP/108	23.2 mm	7.0 mm	114.8 mm	136 mm		
MSR Gold™ 700 SA/2 DE 1CT/4	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 575 SA/2 DE 1CT/40	18.5 mm	5.0 mm	69.6 mm	70.4 mm	70 mm	92 mm
MSR Gold™ 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 1200 SA/2 DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

General Information

Life To 50% Failures (Nom)	750 h
Operating Position	UNIVERSAL

Controls and Dimming

Order Code	Full Product Name	Dimmable
22121000	MSR Gold™ 1200 SA/DE 1CT/4	No
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	No
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	No

Order Code	Full Product Name	Dimmable
21342629	MSR Gold™ 1510 SA/DE UNP/108	Yes
91464100	MSR Gold™ 575 SA/2 DE 1CT/40	No

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
22121000	MSR Gold™ 1200 SA/DE 1CT/4	13.6 A	1200 W
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	11.5 A	700 W
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	13.6 A	1200 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
21342629	MSR Gold™ 1510 SA/DE UNP/108	13.5 A	1510 W
91464100	MSR Gold™ 575 SA/2 DE 1CT/40	7 A	575 W

General Information

MSR Gold™ SA Double Ended


Order Code	Full Product Name	Cap-Base	Main Application	System Description
22121000	MSR Gold™ 1200 SA/DE 1CT/4	SFC10-4	Entertainment	SA/DE
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	SFC10-4	Studio/Disco	SA/2 DE
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	SFC10-4	Entertainment	SA/2 DE

Order Code	Full Product Name	Cap-Base	Main Application	System Description
21342629	MSR Gold™ 1510 SA/DE UNP/108	SFC10-4	Entertainment	SA/DE
91464100	MSR Gold™ 575 SA/2 DE 1CT/40	SFC-11	Entertainment	SA/2 DE

Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour		Colour Rendering		Luminous Flux (Min)	Luminous Flux (Nom)
			Temperature (Nom)	Index (Min)	Index (Nom)			
22121000	MSR Gold™ 1200 SA/DE 1CT/4	-	6000 K	-	85	92700 lm	103000 lm	
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	-	7500 K	62	75	43200 lm	48000 lm	
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	-	7500 K	-	85	90000 lm	100000 lm	
21342629	MSR Gold™ 1510 SA/DE UNP/108	-	6000 K	-	85	-	140000 lm	
91464100	MSR Gold™ 575 SA/2 DE 1CT/40	2	7500 K	-	75	39000 lm	42000 lm	

Colour Rendering Diagrams



XDCR_XDMSR_1200W-Colour Rendering
Vector diagram

