



# CoreLine Projector – The clear choice for LED

## CoreLine Projector

The CoreLine Projector range of luminaires is designed to replace halogen and CDM-standard-based projectors. Their clean lines and attractive TCO help customers to make the switch to LED. These luminaires create a natural lighting effect for use in accent lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install on a standard track or by means of a surface-mount connector.

### Benefits

- Reduced operating costs thanks to energy savings and longer lifetime
- One-to-one replacement, facilitating the switch from conventional to LED luminaires
- Clean, simple finish ensures they blend discreetly into the store interior

### Features

- Smooth black finish with matt aluminum swivel
- Available in 800 and 2400 lumen versions
- Energy-efficient: 70 lm/W
- Integrated driver and passive cooling
- Choice of color temperature: 3000 and 4000 K

### Application

- Independent bakeries
- Independent butcher's stores
- Small grocery stores
- Small fashion stores

# CoreLine Projector

## Specifications

<b>Type</b>	ST120T (3C track version) ST120C (surface mounted version)
<b>Light source</b>	Non-replaceable LED module
<b>Power</b>	11 W (800 lm) 33 W (2400 lm)
<b>Efficacy</b>	70 lm/W
<b>Beam angle</b>	24°
<b>Luminous flux</b>	800 or 2400 lm
<b>Correlated Color</b>	3000 K (Warm white)
<b>Temperature</b>	4000 K (Neutral white)
<b>Color Rendering Index</b>	80
<b>Median useful life</b>	30,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	20,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	10,000 hours
<b>L90B50</b>	

<b>Average ambient temperature</b>	+25 °C
<b>Operating temperature range</b>	0 to +35 °C
<b>Driver</b>	Built-in
<b>Mains voltage</b>	230 or 240 V / 50-60 Hz
<b>Dimming</b>	No dimming
<b>Material</b>	Housing: die-cast aluminum Reflector: plastic Optic: polycarbonate
<b>Color</b>	Black (BK)
<b>Connection</b>	3C track adapter Click Fix Surface Mounting bracket
<b>Installation</b>	On 3-circuit track Individual or in line; clicking the luminaire into pre-screwed ceiling brackets Through-wiring not possible

## Versions



24 °

## Product details



CoreLine\_Projector-  
ST150T-1DPP.TIF



CoreLine\_Projector-  
ST150T-2DPP.TIF

