



# LuxSpace recessed – high efficiency, visual comfort and a stylish design

## LuxSpace, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

# LuxSpace, recessed

## Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Light color: 830, 840, 930 and 827
- Rim colors: high-gloss metalized, white (RAL9010), grey, black (RAL9005) as standard (any other RAL color possible upon request)
- Rimless version available (not for LED40S versions)
- Surface-mounted version available (not for LED40S versions)
- Compliant for central emergency lighting with DC
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring

## Application

- Halls, offices, conference rooms
- Retail
- Hospitals
- Hotels
- Airports
- Museum

## Specifications

<b>Type</b>	DN570B (low height recessed version) DN571B (deep recessed version)
<b>Ceiling type</b>	Plaster (board) ceiling
<b>Light source</b>	Non replaceable LED module
<b>Power</b>	12.6, 21, 25.5, 36 W (3000K) 12.6, 19.8, 24, 36 W (4000K)
<b>Light color:</b>	830, 840, 930 and 827
<b>Luminous flux (for 830 and 840 versions)</b>	DN570B, high-gloss mirror or faceted reflector: 1350, 2200, 2600, 4000 lm DN570B, matt reflector: 1150, 1850, 2200, 4000 lm DN570B, white reflector: 1300, 2100, 2500, 4000 lm DN571B, high-gloss mirror or faceted reflector: 1300, 2100, 2500, 4000 lm DN571B, matt reflector: 1000, 1650, 1950, 4000 lm DN571B, white reflector: 1250, 2000, 2400, 4000 lm
<b>Color Rendering Index</b>	> 80
<b>Median useful life</b>	70,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	50,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	25,000 hours
<b>L90B50</b>	
<b>Average ambient temperature</b>	25 °C

<b>Operating temperature range</b>	+10 to +40 °C
<b>Driver</b>	Separate
<b>Mains voltage</b>	230 or 240 V / 50-60 Hz
<b>Dimming</b>	DALI dimming possible (PSED-E)
<b>Options</b>	Emergency lighting 3 hours (EL3) Protection glass (PG or PGO, IP54 front face) Through-wiring Rimless version for plaster ceiling (not for LED40S) Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR) External or plug-in 3-pole Wieland/Adels connector
<b>Material</b>	Housing and rim: aluminum Reflector: plastic, aluminum coated (for high-gloss and faceted optics)
<b>Color</b>	Rim: white (RAL 9010), grey, black (RAL 9005) or high-gloss metalized
<b>Optic</b>	High-gloss mirror (C) Matt mirror (M) Faceted reflector (F) White reflector (WR)
<b>Connection</b>	Push-in connector or with pull relief
<b>Installation</b>	Fixation by means of spring fasteners
<b>Remarks</b>	External driver included

# LuxSpace, recessed

## Versions



LUXSPACE 2 COMPACT LOW  
HEIGHT - LED Module, system flux  
1200 lm



LUXSPACE 2 COMPACT DEEP -  
LED Module, system flux 1200 lm



LUXSPACE 2 COMPACT LOW  
HEIGHT - LED Module, system flux  
1200 lm



LUXSPACE 2 COMPACT LOW  
HEIGHT - LED Module, system flux  
1200 lm



LUXSPACE 2 COMPACT LOW  
HEIGHT - LED Module, system flux  
1200 lm

## Accessories



Ochranné sklo

Ordercode 93234500



Ochranné sklo opálové

Ordercode 93235200

## Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

## Approval and Application

Mech. impact protection code	IK02
------------------------------	------

## Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

## General Information

CE mark	CE mark
Protection class IEC	Safety class II (II)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	F
Glow-wire test	850/5
Light source replaceable	No
Number of gear units	1 unit

## Initial Performance (IEC Compliant)

Init. Colour rendering index	>80
Luminous flux tolerance	+/-10%

## Mechanical and Housing

Colour	White RAL 9003
--------	----------------

## Application Conditions

Order Code	Full Product Name	Maximum dimming level
96964600	DN570B LED12S/830 PSU-E C EW WH	-
96965300	DN570B LED12S/840 PSU-E C WH	-
96968400	DN570B LED12S/830 DIA-VLC-E C WH	1%
96969100	DN570B LED12S/840 DIA-VLC-E C WH	1%
96972100	DN570B LED20S/830 PSU-E C WH	-
96973800	DN570B LED20S/840 PSU-E C WH	-
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	-
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	-
96980600	DN570B LED20S/830 PSU-E C PG WH	-
96981300	DN570B LED20S/840 PSU-E C PG WH	-
96988200	DN570B LED20S/830 DIA-VLC-E C WH	1%
96989900	DN570B LED20S/840 DIA-VLC-E C WH	1%
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	1%
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	1%
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	1%
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	1%
96998100	DN570B LED24S/830 PSU-E C WH	-
96999800	DN570B LED24S/840 PSU-E C WH	-
97002400	DN570B LED24S/830 DIA-VLC-E C WH	1%
97003100	DN570B LED24S/840 DIA-VLC-E C WH	1%
97006200	DN570B LED24S/830 IA1-E C WH	1%
97007900	DN570B LED24S/840 IA1-E C WH	1%
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	1%
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	1%
97014700	DN570B LED40S/830 PSU-E C WH	-
97015400	DN570B LED40S/840 PSU-E C WH	-
97018500	DN570B LED40S/830 DIA-VLC-E C WH	1%
97019200	DN570B LED40S/840 DIA-VLC-E C WH	1%
97022200	DN570B LED40S/830 IA1-E C WH	1%
97023900	DN570B LED40S/840 IA1-E C WH	1%
97024600	DN570B LED40S/830 IA1-E C ELP3 WH	1%
97025300	DN570B LED40S/840 IA1-E C ELP3 WH	1%
97032100	DN570B LED60S/830 PSU-E C WH	-
97033800	DN570B LED60S/840 PSU-E C WH	-
97034500	DN570B LED60S/830 DIA-VLC-E C WH	1%
97035200	DN570B LED60S/840 DIA-VLC-E C WH	1%
96966000	DN571B LED12S/830 PSU-E C WH	-
96967700	DN571B LED12S/840 PSU-E C WH	-
96970700	DN571B LED12S/830 DIA-VLC-E C WH	1%
96971400	DN571B LED12S/840 DIA-VLC-E C WH	1%
96976900	DN571B LED20S/830 PSU-E C WH	-
96977600	DN571B LED20S/840 PSU-E C WH	-
96978300	DN571B LED20S/830 PSU-E C ELP3 WH	-
96979000	DN571B LED20S/840 PSU-E C ELP3 WH	-
96994300	DN571B LED20S/830 DIA-VLC-E C WH	1%
96995000	DN571B LED20S/840 DIA-VLC-E C WH	1%
96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	1%
96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	1%
97000000	DN571B LED24S/830 PSU-E C WH	-
97001700	DN571B LED24S/840 PSU-E C WH	-
97004800	DN571B LED24S/830 DIA-VLC-E C WH	1%

Order Code	Full Product Name	Maximum dimming level
97005500	DN571B LED24S/840 DIA-VLC-E C WH	1%
97010900	DN571B LED24S/830 IA1-E C WH	1%
97011600	DN571B LED24S/840 IA1-E C WH	1%
97012300	DN571B LED24S/830 IA1-E C ELP3 WH	1%
97013000	DN571B LED24S/840 IA1-E C ELP3 WH	1%
97016100	DN571B LED40S/830 PSU-E C WH	-
97017800	DN571B LED40S/840 PSU-E C WH	-
97020800	DN571B LED40S/830 DIA-VLC-E C WH	1%
97021500	DN571B LED40S/840 DIA-VLC-E C WH	1%
97026000	DN571B LED40S/830 IA1-E C WH	1%
97027700	DN571B LED40S/840 IA1-E C WH	1%
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	1%
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	1%
96982000	DN570B LED20S/830 PSU-E F WH	-
96983700	DN570B LED20S/840 PSU-E F WH	-
96984400	DN570B LED20S/830 PSU-E M WH	-
96985100	DN570B LED20S/840 PSU-E M WH	-
96986800	DN570B LED20S/830 PSU-E WR WH	-
96987500	DN570B LED20S/840 PSU-E WR WH	-

### Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
96964600	DN570B LED12S/830 PSU-E C EW WH	IP20	97023900	DN570B LED40S/840 IA1-E C WH	IP20
96965300	DN570B LED12S/840 PSU-E C WH	IP20	97024600	DN570B LED40S/830 IA1-E C ELP3 WH	IP20
96968400	DN570B LED12S/830 DIA-VLC-E C WH	IP20	97025300	DN570B LED40S/840 IA1-E C ELP3 WH	IP20
96969100	DN570B LED12S/840 DIA-VLC-E C WH	IP20	97032100	DN570B LED60S/830 PSU-E C WH	IP20
96972100	DN570B LED20S/830 PSU-E C WH	IP20	97033800	DN570B LED60S/840 PSU-E C WH	IP20
96973800	DN570B LED20S/840 PSU-E C WH	IP20	97034500	DN570B LED60S/830 DIA-VLC-E C WH	IP20
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	IP20	97035200	DN570B LED60S/840 DIA-VLC-E C WH	IP20
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	IP20	96966000	DN571B LED12S/830 PSU-E C WH	IP20
96980600	DN570B LED20S/830 PSU-E C PG WH	IP54/20	96967700	DN571B LED12S/840 PSU-E C WH	IP20
96981300	DN570B LED20S/840 PSU-E C PG WH	IP54/20	96970700	DN571B LED12S/830 DIA-VLC-E C WH	IP20
96988200	DN570B LED20S/830 DIA-VLC-E C WH	IP20	96971400	DN571B LED12S/840 DIA-VLC-E C WH	IP20
96989900	DN570B LED20S/840 DIA-VLC-E C WH	IP20	96976900	DN571B LED20S/830 PSU-E C WH	IP20
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	IP20	96977600	DN571B LED20S/840 PSU-E C WH	IP20
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	IP20	96978300	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	IP54/20	96979000	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	IP54/20	96994300	DN571B LED20S/830 DIA-VLC-E C WH	IP20
96998100	DN570B LED24S/830 PSU-E C WH	IP20	96995000	DN571B LED20S/840 DIA-VLC-E C WH	IP20
96999800	DN570B LED24S/840 PSU-E C WH	IP20	96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
97002400	DN570B LED24S/830 DIA-VLC-E C WH	IP20	96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
97003100	DN570B LED24S/840 DIA-VLC-E C WH	IP20	97000000	DN571B LED24S/830 PSU-E C WH	IP20
97006200	DN570B LED24S/830 IA1-E C WH	IP20	97001700	DN571B LED24S/840 PSU-E C WH	IP20
97007900	DN570B LED24S/840 IA1-E C WH	IP20	97004800	DN571B LED24S/830 DIA-VLC-E C WH	IP20
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	IP20	97005500	DN571B LED24S/840 DIA-VLC-E C WH	IP20
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	IP20	97010900	DN571B LED24S/830 IA1-E C WH	IP20
97014700	DN570B LED40S/830 PSU-E C WH	IP20	97011600	DN571B LED24S/840 IA1-E C WH	IP20
97015400	DN570B LED40S/840 PSU-E C WH	IP20	97012300	DN571B LED24S/830 IA1-E C ELP3 WH	IP20
97018500	DN570B LED40S/830 DIA-VLC-E C WH	IP20	97013000	DN571B LED24S/840 IA1-E C ELP3 WH	IP20
97019200	DN570B LED40S/840 DIA-VLC-E C WH	IP20	97016100	DN571B LED40S/830 PSU-E C WH	IP20
97022200	DN570B LED40S/830 IA1-E C WH	IP20	97017800	DN571B LED40S/840 PSU-E C WH	IP20

Order Code	Full Product Name	Ingress protection code
97020800	DN571B LED40S/830 DIA-VLC-E C WH	IP20
97021500	DN571B LED40S/840 DIA-VLC-E C WH	IP20
97026000	DN571B LED40S/830 IA1-E C WH	IP20
97027700	DN571B LED40S/840 IA1-E C WH	IP20
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	IP20
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	IP20

Order Code	Full Product Name	Ingress protection code
96982000	DN570B LED20S/830 PSU-E F WH	IP20
96983700	DN570B LED20S/840 PSU-E F WH	IP20
96984400	DN570B LED20S/830 PSU-E M WH	IP20
96985100	DN570B LED20S/840 PSU-E M WH	IP20
96986800	DN570B LED20S/830 PSU-E WR WH	IP20
96987500	DN570B LED20S/840 PSU-E WR WH	IP20

## Controls and Dimming

Order Code	Full Product Name	Dimmable
96964600	DN570B LED12S/830 PSU-E C EW WH	No
96965300	DN570B LED12S/840 PSU-E C WH	No
96968400	DN570B LED12S/830 DIA-VLC-E C WH	Yes
96969100	DN570B LED12S/840 DIA-VLC-E C WH	Yes
96972100	DN570B LED20S/830 PSU-E C WH	No
96973800	DN570B LED20S/840 PSU-E C WH	No
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	No
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	No
96980600	DN570B LED20S/830 PSU-E C PG WH	No
96981300	DN570B LED20S/840 PSU-E C PG WH	No
96988200	DN570B LED20S/830 DIA-VLC-E C WH	Yes
96989900	DN570B LED20S/840 DIA-VLC-E C WH	Yes
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	Yes
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	Yes
96998100	DN570B LED24S/830 PSU-E C WH	No
96999800	DN570B LED24S/840 PSU-E C WH	No
97002400	DN570B LED24S/830 DIA-VLC-E C WH	Yes
97003100	DN570B LED24S/840 DIA-VLC-E C WH	Yes
97006200	DN570B LED24S/830 IA1-E C WH	Yes
97007900	DN570B LED24S/840 IA1-E C WH	Yes
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	Yes
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	Yes
97014700	DN570B LED40S/830 PSU-E C WH	No
97015400	DN570B LED40S/840 PSU-E C WH	No
97018500	DN570B LED40S/830 DIA-VLC-E C WH	Yes
97019200	DN570B LED40S/840 DIA-VLC-E C WH	Yes
97022200	DN570B LED40S/830 IA1-E C WH	Yes
97023900	DN570B LED40S/840 IA1-E C WH	Yes
97024600	DN570B LED40S/830 IA1-E C ELP3 WH	Yes
97025300	DN570B LED40S/840 IA1-E C ELP3 WH	Yes
97032100	DN570B LED60S/830 PSU-E C WH	No
97033800	DN570B LED60S/840 PSU-E C WH	No
97034500	DN570B LED60S/830 DIA-VLC-E C WH	Yes

Order Code	Full Product Name	Dimmable
97035200	DN570B LED60S/840 DIA-VLC-E C WH	Yes
96966000	DN571B LED12S/830 PSU-E C WH	No
96967700	DN571B LED12S/840 PSU-E C WH	No
96970700	DN571B LED12S/830 DIA-VLC-E C WH	Yes
96971400	DN571B LED12S/840 DIA-VLC-E C WH	Yes
96976900	DN571B LED20S/830 PSU-E C WH	No
96977600	DN571B LED20S/840 PSU-E C WH	No
96978300	DN571B LED20S/830 PSU-E C ELP3 WH	No
96979000	DN571B LED20S/840 PSU-E C ELP3 WH	No
96994300	DN571B LED20S/830 DIA-VLC-E C WH	Yes
96995000	DN571B LED20S/840 DIA-VLC-E C WH	Yes
96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
97000000	DN571B LED24S/830 PSU-E C WH	No
97001700	DN571B LED24S/840 PSU-E C WH	No
97004800	DN571B LED24S/830 DIA-VLC-E C WH	Yes
97005500	DN571B LED24S/840 DIA-VLC-E C WH	Yes
97010900	DN571B LED24S/830 IA1-E C WH	Yes
97011600	DN571B LED24S/840 IA1-E C WH	Yes
97012300	DN571B LED24S/830 IA1-E C ELP3 WH	Yes
97013000	DN571B LED24S/840 IA1-E C ELP3 WH	Yes
97016100	DN571B LED40S/830 PSU-E C WH	No
97017800	DN571B LED40S/840 PSU-E C WH	No
97020800	DN571B LED40S/830 DIA-VLC-E C WH	Yes
97021500	DN571B LED40S/840 DIA-VLC-E C WH	Yes
97026000	DN571B LED40S/830 IA1-E C WH	Yes
97027700	DN571B LED40S/840 IA1-E C WH	Yes
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	Yes
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	Yes
96982000	DN570B LED20S/830 PSU-E F WH	No
96983700	DN570B LED20S/840 PSU-E F WH	No
96984400	DN570B LED20S/830 PSU-E M WH	No
96985100	DN570B LED20S/840 PSU-E M WH	No
96986800	DN570B LED20S/830 PSU-E WR WH	No
96987500	DN570B LED20S/840 PSU-E WR WH	No

## General Information

Order Code	Full Product Name	Optic type	Product family code
96964600	DN570B LED12S/830 PSU-E C EW WH	C	DN570B

Order Code	Full Product Name	Optic type	Product family code
96965300	DN570B LED12S/840 PSU-E C WH	C	DN570B

Order Code	Full Product Name	Optic type	Product family code
96968400	DN570B LED12S/830 DIA-VLC-E C WH	C	DN570B
96969100	DN570B LED12S/840 DIA-VLC-E C WH	C	DN570B
96972100	DN570B LED20S/830 PSU-E C WH	C	DN570B
96973800	DN570B LED20S/840 PSU-E C WH	C	DN570B
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	C	DN570B
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	C	DN570B
96980600	DN570B LED20S/830 PSU-E C PG WH	C	DN570B
96981300	DN570B LED20S/840 PSU-E C PG WH	C	DN570B
96988200	DN570B LED20S/830 DIA-VLC-E C WH	C	DN570B
96989900	DN570B LED20S/840 DIA-VLC-E C WH	C	DN570B
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	C	DN570B
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	C	DN570B
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	C	DN570B
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	C	DN570B
96998100	DN570B LED24S/830 PSU-E C WH	C	DN570B
96999800	DN570B LED24S/840 PSU-E C WH	C	DN570B
97002400	DN570B LED24S/830 DIA-VLC-E C WH	C	DN570B
97003100	DN570B LED24S/840 DIA-VLC-E C WH	C	DN570B
97006200	DN570B LED24S/830 IA1-E C WH	C	DN570B
97007900	DN570B LED24S/840 IA1-E C WH	C	DN570B
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	C	DN570B
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	C	DN570B
97014700	DN570B LED40S/830 PSU-E C WH	C	DN570B
97015400	DN570B LED40S/840 PSU-E C WH	C	DN570B
97018500	DN570B LED40S/830 DIA-VLC-E C WH	C	DN570B
97019200	DN570B LED40S/840 DIA-VLC-E C WH	C	DN570B
97022200	DN570B LED40S/830 IA1-E C WH	C	DN570B
97023900	DN570B LED40S/840 IA1-E C WH	C	DN570B
97024600	DN570B LED40S/830 IA1-E C ELP3 WH	C	DN570B
97025300	DN570B LED40S/840 IA1-E C ELP3 WH	C	DN570B
97032100	DN570B LED60S/830 PSU-E C WH	C	DN570B
97033800	DN570B LED60S/840 PSU-E C WH	C	DN570B
97034500	DN570B LED60S/830 DIA-VLC-E C WH	C	DN570B
97035200	DN570B LED60S/840 DIA-VLC-E C WH	C	DN570B
96966000	DN571B LED12S/830 PSU-E C WH	C	DN571B

Order Code	Full Product Name	Optic type	Product family code
96967700	DN571B LED12S/840 PSU-E C WH	C	DN571B
96970700	DN571B LED12S/830 DIA-VLC-E C WH	C	DN571B
96971400	DN571B LED12S/840 DIA-VLC-E C WH	C	DN571B
96976900	DN571B LED20S/830 PSU-E C WH	C	DN571B
96977600	DN571B LED20S/840 PSU-E C WH	C	DN571B
96978300	DN571B LED20S/830 PSU-E C ELP3 WH	C	DN571B
96979000	DN571B LED20S/840 PSU-E C ELP3 WH	C	DN571B
96994300	DN571B LED20S/830 DIA-VLC-E C WH	C	DN571B
96995000	DN571B LED20S/840 DIA-VLC-E C WH	C	DN571B
96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	C	DN571B
96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	C	DN571B
97000000	DN571B LED24S/830 PSU-E C WH	C	DN571B
97001700	DN571B LED24S/840 PSU-E C WH	C	DN571B
97004800	DN571B LED24S/830 DIA-VLC-E C WH	C	DN571B
97005500	DN571B LED24S/840 DIA-VLC-E C WH	C	DN571B
97010900	DN571B LED24S/830 IA1-E C WH	C	DN571B
97011600	DN571B LED24S/840 IA1-E C WH	C	DN571B
97012300	DN571B LED24S/830 IA1-E C ELP3 WH	C	DN571B
97013000	DN571B LED24S/840 IA1-E C ELP3 WH	C	DN571B
97016100	DN571B LED40S/830 PSU-E C WH	C	DN571B
97017800	DN571B LED40S/840 PSU-E C WH	C	DN571B
97020800	DN571B LED40S/830 DIA-VLC-E C WH	C	DN571B
97021500	DN571B LED40S/840 DIA-VLC-E C WH	C	DN571B
97026000	DN571B LED40S/830 IA1-E C WH	C	DN571B
97027700	DN571B LED40S/840 IA1-E C WH	C	DN571B
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	C	DN571B
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	C	DN571B
96982000	DN570B LED20S/830 PSU-E F WH	F	DN570B
96983700	DN570B LED20S/840 PSU-E F WH	F	DN570B
96984400	DN570B LED20S/830 PSU-E M WH	Matt optic decorative	DN570B
96985100	DN570B LED20S/840 PSU-E M WH	Matt optic decorative	DN570B
96986800	DN570B LED20S/830 PSU-E WR WH	C	DN570B
96987500	DN570B LED20S/840 PSU-E WR WH	C	DN570B

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96964600	DN570B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
96965300	DN570B LED12S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96968400	DN570B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
96969100	DN570B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm

## LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96972100	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96973800	DN570B LED20S/840 PSU-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
96980600	DN570B LED20S/830 PSU-E C PG WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96981300	DN570B LED20S/840 PSU-E C PG WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96988200	DN570B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96989900	DN570B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96998100	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96999800	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97002400	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
97003100	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97006200	DN570B LED24S/830 IA1-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
97007900	DN570B LED24S/840 IA1-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	121 lm/W	2600 lm
97014700	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
97015400	DN570B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97018500	DN570B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
97019200	DN570B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97022200	DN570B LED40S/830 IA1-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
97023900	DN570B LED40S/840 IA1-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97024600	DN570B LED40S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	122 lm/W	4400 lm



## LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
97025300	DN570B LED40S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	133 lm/W	4400 lm
97032100	DN570B LED60S/830 PSU-E C WH	(0.43, 0.40)	3000 K	129 lm/W	6200 lm
97033800	DN570B LED60S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	6200 lm
97034500	DN570B LED60S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	129 lm/W	6200 lm
97035200	DN570B LED60S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	6200 lm
96966000	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
96967700	DN571B LED12S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm
96970700	DN571B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
96971400	DN571B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm
96976900	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96977600	DN571B LED20S/840 PSU-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96978300	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
96979000	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
96994300	DN571B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96995000	DN571B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
97000000	DN571B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
97001700	DN571B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97004800	DN571B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
97005500	DN571B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97010900	DN571B LED24S/830 IA1-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
97011600	DN571B LED24S/840 IA1-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
97012300	DN571B LED24S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm
97013000	DN571B LED24S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	121 lm/W	2600 lm
97016100	DN571B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
97017800	DN571B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97020800	DN571B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm

## LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
97021500	DN571B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97026000	DN571B LED40S/830 IA1-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
97027700	DN571B LED40S/840 IA1-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	122 lm/W	4400 lm
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	133 lm/W	4400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
96982000	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96983700	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
96984400	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40)	3000 K	113 lm/W	1860 lm
96985100	DN570B LED20S/840 PSU-E M WH	(0.38, 0.38)	4000 K	127 lm/W	1860 lm
96986800	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
96987500	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
96964600	DN570B LED12S/830 PSU-E C EW WH	9,9 W
96965300	DN570B LED12S/840 PSU-E C WH	9,2 W
96968400	DN570B LED12S/830 DIA-VLC-E C WH	9,9 W
96969100	DN570B LED12S/840 DIA-VLC-E C WH	9,2 W
96972100	DN570B LED20S/830 PSU-E C WH	16,4 W
96973800	DN570B LED20S/840 PSU-E C WH	14,8 W
96974500	DN570B LED20S/830 PSU-E C ELP3 WH	19,4 W
96975200	DN570B LED20S/840 PSU-E C ELP3 WH	17,8 W
96980600	DN570B LED20S/830 PSU-E C PG WH	16,4 W
96981300	DN570B LED20S/840 PSU-E C PG WH	14,8 W
96988200	DN570B LED20S/830 DIA-VLC-E C WH	16,4 W
96989900	DN570B LED20S/840 DIA-VLC-E C WH	14,8 W
96990500	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	19,4 W
96991200	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	17,8 W
96992900	DN570B LED20S/830 DIA-VLC-E C PG WH	16,4 W
96993600	DN570B LED20S/840 DIA-VLC-E C PG WH	14,8 W
96998100	DN570B LED24S/830 PSU-E C WH	20 W
96999800	DN570B LED24S/840 PSU-E C WH	18,4 W
97002400	DN570B LED24S/830 DIA-VLC-E C WH	20 W
97003100	DN570B LED24S/840 DIA-VLC-E C WH	18,4 W
97006200	DN570B LED24S/830 IA1-E C WH	20 W
97007900	DN570B LED24S/840 IA1-E C WH	18,4 W
97008600	DN570B LED24S/830 IA1-E C ELP3 WH	23 W
97009300	DN570B LED24S/840 IA1-E C ELP3 WH	21,4 W
97014700	DN570B LED40S/830 PSU-E C WH	33 W
97015400	DN570B LED40S/840 PSU-E C WH	30 W
97018500	DN570B LED40S/830 DIA-VLC-E C WH	33 W
97019200	DN570B LED40S/840 DIA-VLC-E C WH	30 W

Order Code	Full Product Name	Initial input power
97022200	DN570B LED40S/830 IA1-E C WH	33 W
97023900	DN570B LED40S/840 IA1-E C WH	30 W
97024600	DN570B LED40S/830 IA1-E C ELP3 WH	36 W
97025300	DN570B LED40S/840 IA1-E C ELP3 WH	33 W
97032100	DN570B LED60S/830 PSU-E C WH	48 W
97033800	DN570B LED60S/840 PSU-E C WH	44 W
97034500	DN570B LED60S/830 DIA-VLC-E C WH	48 W
97035200	DN570B LED60S/840 DIA-VLC-E C WH	44 W
96966000	DN571B LED12S/830 PSU-E C WH	9,9 W
96967700	DN571B LED12S/840 PSU-E C WH	9,2 W
96970700	DN571B LED12S/830 DIA-VLC-E C WH	9,9 W
96971400	DN571B LED12S/840 DIA-VLC-E C WH	9,2 W
96976900	DN571B LED20S/830 PSU-E C WH	16,4 W
96977600	DN571B LED20S/840 PSU-E C WH	14,8 W
96978300	DN571B LED20S/830 PSU-E C ELP3 WH	19,4 W
96979000	DN571B LED20S/840 PSU-E C ELP3 WH	17,8 W
96994300	DN571B LED20S/830 DIA-VLC-E C WH	16,4 W
96995000	DN571B LED20S/840 DIA-VLC-E C WH	14,8 W
96996700	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	19,4 W
96997400	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	17,8 W
97000000	DN571B LED24S/830 PSU-E C WH	20 W
97001700	DN571B LED24S/840 PSU-E C WH	18,4 W
97004800	DN571B LED24S/830 DIA-VLC-E C WH	20 W
97005500	DN571B LED24S/840 DIA-VLC-E C WH	18,4 W
97010900	DN571B LED24S/830 IA1-E C WH	20 W
97011600	DN571B LED24S/840 IA1-E C WH	18,4 W
97012300	DN571B LED24S/830 IA1-E C ELP3 WH	23 W
97013000	DN571B LED24S/840 IA1-E C ELP3 WH	21,4 W

## LuxSpace, recessed

Order Code	Full Product Name	Initial input power
97016100	DN571B LED40S/830 PSU-E C WH	33 W
97017800	DN571B LED40S/840 PSU-E C WH	30 W
97020800	DN571B LED40S/830 DIA-VLC-E C WH	33 W
97021500	DN571B LED40S/840 DIA-VLC-E C WH	30 W
97026000	DN571B LED40S/830 IA1-E C WH	33 W
97027700	DN571B LED40S/840 IA1-E C WH	30 W
97028400	DN571B LED40S/830 IA1-E C ELP3 WH	36 W

Order Code	Full Product Name	Initial input power
97029100	DN571B LED40S/840 IA1-E C ELP3 WH	33 W
96982000	DN570B LED20S/830 PSU-E F WH	16,4 W
96983700	DN570B LED20S/840 PSU-E F WH	14,8 W
96984400	DN570B LED20S/830 PSU-E M WH	16,4 W
96985100	DN570B LED20S/840 PSU-E M WH	14,8 W
96986800	DN570B LED20S/830 PSU-E WR WH	16,4 W
96987500	DN570B LED20S/840 PSU-E WR WH	14,8 W

