



CityCharm Cordoba - combining ambiance and optimum performance

CityCharm Cordoba

CityCharm Cordoba is designed for use in urban areas where comfortable lighting, ambiance and design play an important role. Its unobtrusive appearance makes it a timeless, future-proof luminaire that is ideal for residential areas, parks, footpaths and cycle lanes, where visual comfort and maximum efficiency are key. CityCharm offers a choice of two iconic designs (Cordoba and Cone) and various accessories, enabling you to create a lighting solution that carries your signature, both by day and by night. CityCharm luminaires are also available as a complete set, with a choice of dedicated poles and brackets.

Benefits

- Elegant iconic range focused on comfortable lighting
- Future-proof due to excellent lighting performance and high quality of product and finishing
- Suitable for both renovation projects and new installations thanks to dedicated brackets and

Features

- Choice of luminaire shapes, color effects, and dedicated poles and brackets
- Diffusing tools to create visual comfort and colored parts to enhance ambiance
- A broad lumen range and optics to ensure maximum efficiency at all lighting levels
- Optimized total cost of ownership
- Compatible with all standard and advanced Philips lighting systems and CityTouch Ready
- Easy on-site maintenance of the driver

Application

- Residential areas
- Footpaths and cycle lanes
- Parks and boulevards

Specifications

Type	BDS490
Light source	Built-in LED-module
Power	10-82 W (3000 K) 9-75 W (4000 K)
Luminous flux	1100-7400 lm (3000 K) 1100-7450 lm (4000 K)
Luminaire efficacy	120 lm/W (3000 K) 130 lm/W (4000 K)
Correlated Color	3000 K, warm white (WW)
Temperature	4000 K, neutral white (NW)
Color Rendering Index	≥ 80 (3000 K) ≥ 70 (4000 K)
Maintenance of lumen output - L80B10	100,000 hours
Operating temperature range	-20 to +35 °C
Driver	Built-in (self ballasted LED-module)
Mains voltage	220-240 V / 50-60 Hz
Inrush current	28 A / 150 μs (27 W Xitanium driver) 27 A / 150 μs (40 W Xitanium driver) 80 A / 150 μs (100 W Xitanium driver)

Dimming	DynaDimmer LumiStep CLO
Controls system input	DALI
Options	Photocell: Minicell, 35, 55, 70 lux
Optic	Distribution medium (DM), wide (DW), vertical (DV), symmetrical (S), asymmetrical (A)
Optical element	Louver (option)
Optical cover	Diffusing plates (two different plates available)
Material	Housing: high-pressure die-cast aluminum, non corrosive Bowl: polycarbonate, reinforced against UV
Color	Housing: Philips ultra-dark grey (close to RAL 7022, fine textured color) Other RAL and AKZO Futura colors available on request
Maintenance	Easy access to the driver from the top, 3 screws
Installation	Post-top mounting: Ø 60-76 mm, two screws Recommended mounting height: 4-6 m Max SCx: 0.1124 m
Accessories	JDP490 (CityCharm post-top bracket) JPP490 (CityCharm bracket) YHM490 (CityCharm pole)

Versions



CityCharm Cordoba BDS490
bybelysningsarmatur med
ClearGuide

CityCharm Cordoba

Product details



CityCharm_Cordoba-
BDS490_DGR-DP01.tif



CityCharm_Cordoba_Cone-
BDS490_BDS491_DGR-DP02.tif

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Approval and Application

Mech. impact protection code	IK10
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode

Controls and Dimming

Dimmable	No
----------	----

General Information

Luminaire light beam spread	360°
CE mark	CE mark
Light source colour	730 warm white
Optical cover/lens type	PC
Driver included	Yes
Flammability mark	NO
Gear	EB
Glow-wire test	650/5
Light source replaceable	Yes
Number of gear units	1 unit
Number of light sources	15
Product Family Code	BDS490
UL mark	-

Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature	3000 K
Init. Colour Rendering Index	≥70

Light Technical

Scotopic/photopic lumen ratio	1.24
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0.03

Mechanical and Housing

Colour	Gray
--------	------

Operating and Electrical

Order Code	Full Product Name	Driver current
93920800	BDS490 CG25-/730 II A GR D11 76	447 mA
93922200	BDS490 CG20-/730 II S GR CLO C6K FQQ-PX1	344 mA
93923900	BDS490 CG25-/730 II S GR CLO C6K FQQ-PX1	447 mA
93924600	BDS490 CG30-/730 II S GR CLO C6K FQQ-PX1	553 mA

General Information

Order Code	Full Product Name	Coating	Lamp family code	Optic type
93920800	BDS490 CG25-/730 II A GR D11 76	-	CG25	Asymmetrical
93922200	BDS490 CG20-/730 II S GR CLO C6K FQQ-PX1	-	CG20	Symmetrical
93923900	BDS490 CG25-/730 II S GR CLO C6K FQQ-PX1	-	CG25	Symmetrical

Order Code	Full Product Name	Coating	Lamp family code	Optic type
93924600	BDS490 CG30-/730 II S GR CLO C6K FQQ-PX1	-	CG30	Symmetrical

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux	Order Code	Full Product Name	Initial luminous flux
93920800	BDS490 CG25-/730 II A GR D11 76	2117 lm	93923900	BDS490 CG25-/730 II S GR CLO C6K FQQ-PX1	2117 lm
93922200	BDS490 CG20-/730 II S GR CLO C6K FQQ-PX1	1696 lm	93924600	BDS490 CG30-/730 II S GR CLO C6K FQQ-PX1	2543 lm

