

PowerBalance gen2

RC461B LED40S/940 PSD W30L120 VPC W

PowerBalance recessed - Generation 2 - LED Module, system flux 4000 lm - 940 neutral white - Power supply unit with DALI interface - Width 0.30 m, length 1.20 m - Visible profile ceiling version - Plug-in connector 3-pole Wieland/Adels compatible -

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance gen2 is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. The gen2 architecture enables a range of highly versatile modular and semi-modular luminaires. These luminaires can be easily mounted in ceilings with exposed T-bar and concealed T-bar, as well as plaster ceilings and bandraaster-type ceilings. PowerBalance is also available in a surface-mounted version.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

Product data

General Information	
Number of light sources	1 [1 pc]

Lamp family code	LED40S [LED Module, system flux 4000 lm]
Beam angle of light source	120 °

PowerBalance gen2

Light source colour	940 neutral white
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	No [-]
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Luminaire light beam spread	86°
Control interface	DALI
Connection	W [Plug-in connector 3-pole Wieland/ Adels compatible]
Cable	-
Protection class IEC	Safety class I (I)
Glow-wire test	850/5 [Temperature 850 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Glare-shielding accessories	No [-]
Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	RC461B [PowerBalance recessed]
Unified glare rating CEN	16

Light Technical

Saturated Red	>50
---------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Geometry	W30L120 [Width 0.30 m, length 1.20 m]
Housing configuration	VPC [Visible profile ceiling version]
Housing material	Steel
Reflector material	Polycarbonate
Optic material	-
Optical cover/lens material	Polycarbonate

Gear tray material	Steel
Fixation material	-
Optical cover/lens finish	Matte
Overall length	1197 mm
Overall width	297 mm
Overall height	79 mm
Colour	White
Dimensions (height x width x depth)	79 x 297 x 1197 mm (3.1 x 11.7 x 47.1 in)

Approval and Application

Ingress protection code	IP20 (front IP40)
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	4000 lm
Initial luminous flux at colour temperature of 4,000 K	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥90
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	28.5 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90

Application Conditions

Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No


Product Data

Full product code	871869996444300
Order product name	RC461B LED40S/940 PSD W30L120 VPC W
EAN/UPC – product	8718699964443
Order code	96444300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910505100238
SAP net weight (piece)	5.300 kg




PowerBalance gen2

Dimensional drawing




PowerBalance RC460B-RC468B

Photometric data



IFGU1_RC461BPSDW30L1201xLED40S940



OFPC1_RC461BPSDW30L1201xLED40S940

