



TrueLine, recessed

RC530B LED50S/940 W8L145 PCV ELP3 PI6

TrueLine Recessed OC - 940 neutral white - Power supply unit with DALI interface - Push-in connector 6-pole - White RAL 9003

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in a suspended version.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

Product data

General Information		Control interface	DALI
Beam angle of light source	- °	Connection	PI6 [Push-in connector 6-pole]
Light source colour	940 neutral white	Cable	-
Light source replaceable	No	Protection class IEC	Safety class I (I)
Number of gear units	1 unit	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Flammability mark	F [For mounting on normally flammable surfaces]
Driver included	Yes	CE mark	CE mark
Optic type	No [-]	ENEC mark	ENEC mark
Luminaire light beam spread	100°	Warranty period	5 years

TrueLine, recessed

Constant light output	No
Number of products on MCB (16 A type B)	24
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes
Product family code	RC530B [TrueLine Recessed OC]
Unified glare rating CEN	19

Light Technical

Saturated Red (R9)	>50
--------------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	-
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	1450 mm
Overall width	115 mm
Overall height	136 mm
Colour	White RAL 9003
Dimensions (height x width x depth)	136 x 115 x 1450 mm (5.4 x 4.5 x 57.1 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	--------------------------

Mech. impact protection code	IK02 [0.2 J standard]
------------------------------	------------------------

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	5000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	135 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>90
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	37 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L85

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No

Product Data

Full product code	871869996576100
Order product name	RC530B LED50S/940 W8L145 PCV ELP3 P16
EAN/UPC – product	8718699965761
Order code	96576100
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	910505100387
Net Weight (Piece)	4.100 kg





Dimensional drawing



TrueLine recessed RC515B, RC530B-RC534B

TrueLine, recessed

Photometric data



IFGU1_RC530BPSDW8L145ELP31xLED505/940OC

OFPC1_RC530BPSDW8L145ELP31xLED505/940OC

