

# PowerBalance gen2

## RC463B LED40S/930 PSD W31L125 VPC PIP

PowerBalance recessed - 930 warm white - Power supply unit with DALI interface - Push-in connector and pull relief - -

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance gen2 is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. The gen2 architecture enables a range of highly versatile modular and semi-modular luminaires. These luminaires can be easily mounted in ceilings with exposed T-bar and concealed T-bar, as well as plaster ceilings and bandraaster-type ceilings. PowerBalance is also available in a surface-mounted version.

### Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

### Product data

General information	
Beam angle of light source	120 °
Light source colour	930 warm white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]

Driver included	Yes
Optic type	No [-]
Luminaire light beam spread	86°
Control interface	DALI
Connection	PIP [ Push-in connector and pull relief]
Cable	-
Protection class IEC	Safety class I (I)

## PowerBalance gen2

Glow-wire test	850/5 [ Temperature 850 °C, duration 5 s]
Flammability mark	F [ For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	RC463B [ PowerBalance recessed]
Unified glare rating CEN	16

### Light Technical

Saturated Red	>50
---------------	-----

### Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Steel
Reflector material	Polycarbonate
Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Matte
Overall length	1222 mm
Overall width	322 mm
Overall height	79 mm
Colour	White RAL 9003
Dimensions (height x width x depth)	79 x 322 x 1222 mm (3.1 x 12.7 x 48.1 in)

### Approval and Application

Ingress protection code	IP20 (front IP40)
-------------------------	-------------------

Mech. impact protection code	IK02 [ 0.2 J standard]
------------------------------	------------------------

### Initial Performance (IEC Compliant)

Initial luminous flux	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	133 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	≥90
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	30 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90

### Application Conditions

Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No


### Product Data

Full product code	871869996612600
Order product name	RC463B LED40S/930 PSD W31L125 VPC PIP
EAN/UPC – product	8718699966126
Order code	96612600
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910505100424
SAP net weight (piece)	5.800 kg




# PowerBalance gen2

## Dimensional drawing




PowerBalance RC460B-RC468B

## Photometric data



OFPC1\_RC463BPSUW31L1251xLED40S930



IFGU1\_RC463BPSUW31L1251xLED40S930

