



# TrueLine, recessed

## RC532B LED43S/940 PSD W8L141 PCV PI5

TrueLine Recessed Line OC - 940 neutral white - Power supply unit with DALI interface - Push-in connector 5-pole (PI) - White RAL 9003

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in a suspended version.

### Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

### Product data

General Information			
Beam angle of light source	- °	Control interface	DALI
Light source colour	940 neutral white	Connection	Push-in connector 5-pole (PI)
Light source replaceable	No	Cable	-
Number of gear units	1 unit	Protection class IEC	Safety class I (I)
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Driver included	Yes	Flammability mark	F [ For mounting on normally flammable surfaces]
Optic type	No [ -]	CE mark	CE mark
Luminaire light beam spread	100°	ENEC mark	ENEC mark
		Warranty period	5 years

## TrueLine, recessed

Constant light output	No
Number of products on MCB (16 A type B)	24
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes
Product family code	RC532B [ TrueLine Recessed Line OC ]
Unified glare rating CEN	19

### Light Technical

Saturated Red	>50
---------------	-----

### Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	-
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	1410 mm
Overall width	115 mm
Overall height	136 mm
Colour	White RAL 9003
Dimensions (height x width x depth)	136 x 115 x 1410 mm (5.4 x 4.5 x 55.5 in)

### Approval and Application

Ingress protection code	IP20 [ Finger-protected ]
-------------------------	---------------------------

Mech. impact protection code	IK02 [ 0.2 J standard ]
------------------------------	-------------------------

### Initial Performance (IEC Compliant)

Initial luminous flux	4300 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	152 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>90
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	28.5 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 5 %	50,000 h
Lumen maintenance at median useful life*	L85
	50,000 h

### Application Conditions

Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No

### Product Data

Full product code	871869996617100
Order product name	RC532B LED43S/940 PSD W8L141 PCV P15
EAN/UPC – product	8718699966171
Order code	96617100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910505100429
SAP net weight (piece)	3.200 kg



## Dimensional drawing



TrueLine recessed RC515B, RC530B-RC534B

