



CoreLine Trunking

LL121X LED80S/840 PSU WB TW3 SMB WH KIT

CoreLine Trunking - 3 pcs - LED Module, system flux 8000 lm - Power supply unit - Wide beam - - - - - Ceiling-mounting bracket - White - - - -

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Protection class IEC	Safety class I (I)
Number of light sources	3 [3 pcs]	Mounting	SMB [Ceiling-mounting bracket]
Lamp family code	LED80S [LED Module, system flux 8000 lm]	Ready-to-install	-
Beam angle of light source	120 °	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Light source colour	840 neutral white	Flammability mark	F [For mounting on normally flammable surfaces]
Light source replaceable	No	Accessories included	MB-SW [Mounting bracket for suspension wire]
Number of gear units	1 unit	CE mark	CE mark
Driver/power unit/transformer	PSU [Power supply unit]	ENEC mark	ENEC mark
Driver included	Yes	Mechanical accessories	No [-]
Optic type	WB [Wide beam]	Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10.
Optical cover/lens type	No [-]		
Luminaire light beam spread	100° x 94°		
Emergency lighting	No [-]		
Control interface	-		
Internal wiring	Standard		
Connection	CU5 [Connection unit 5-pole]		
Cable	-		

CoreLine Trunking

	Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	LL121X [CoreLine Trunking]
Unified glare rating CEN	Not applicable

Light Technical

Light distribution	DIR [Direct lighting]
--------------------	------------------------

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	No [-]
Circuit option	No [-]
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.97

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	1730 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-
Colour	White
Dimensions (height x width x depth)	52 x 95 x 1730 mm (2 x 3.7 x 68.1 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	8000 lm
Luminous flux tolerance	+/-1%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	54 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

Product Data

Full product code	871869638080200
Order product name	LL121X LED80S/840 PSU WB TW3 SMB WH KIT
EAN/UPC – product	8718696380802
Order code	38080200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910925863959
SAP net weight (piece)	3.870 kg





CoreLine Trunking

Dimensional drawing

//

CoreLine electr. units LL120X-LL122X

Photometric data



IFGU1_LL121X1xLED80S840WB

IFPC1_LL121X1xLED80S840WB

