



# CoreLine Trunking

## LL120X LED160S/840 2x PSD WB 7X2.5 VLC W

CoreLine Trunking - 6 pcs - LED module, system flux 16000 lm - Power supply unit with DALI interface - Wide beam - - - 7 conductors cross-section 2.5 mm<sup>2</sup> - - - Ceiling-mounting bracket - White - - - -

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information		Cable	-
Number of light sources	6 [ 6 pcs]	Protection class IEC	Safety class I (I)
Lamp family code	LED160S [ LED module, system flux 16000 lm]	Mounting	SMB [ Ceiling-mounting bracket]
Beam angle of light source	120 °	Ready-to-install	-
Light source colour	840 neutral white	Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Light source replaceable	No	Flammability mark	F [ For mounting on normally flammable surfaces]
Number of gear units	2 units	Accessories included	MB-SW [ Mounting bracket for suspension wire]
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	CE mark	CE mark
Driver included	Yes	ENEC mark	ENEC mark
Optic type	WB [ Wide beam]	Mechanical accessories	No [ -]
Optical cover/lens type	No [ -]	Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance
Luminaire light beam spread	100° x 94°		
Emergency lighting	No [ -]		
Control interface	DALI		
Internal wiring	Standard		
Connection	CU7 [ Connection unit 7-pole]		

## CoreLine Trunking

	between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
--	---

Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	LL120X [ CoreLine Trunking]
Unified glare rating CEN	Not applicable

### Light Technical

Light distribution	DIR [ Direct lighting]
--------------------	------------------------

### Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	No [ -]
Circuit option	7x2.5 [ 7 conductors cross-section 2.5 mm <sup>2</sup> ]
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	22 A
Inrush time	0.275 ms
Power factor (min.)	0.97

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	3450 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-
Colour	White

Dimensions (height x width x depth)	52 x 95 x 3450 mm (2 x 3.7 x 135.8 in)
-------------------------------------	--

### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	16000 lm
Luminous flux tolerance	+/-2%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	108 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

### Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No


### Product Data

Full product code	871869638086400
Order product name	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W
EAN/UPC – product	8718696380864
Order code	38086400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12 NC)	910925863965
SAP net weight (piece)	7.490 kg





# CoreLine Trunking

## Dimensional drawing



### CoreLine electr. units LL120X-LL122X

## Photometric data



### IFGU1\_LL120X1xLED160S840WB

### IFPC1\_LL120X1xLED160S840WB

