



CoreLine Trunking

LL121X LED80S/840 1x PSU WB 5 WH

CoreLine Trunking - 3 pcs - LED Module, system flux 8000 lm - Power supply unit - Wide beam - - - 5 conductors - - - Feed-through wiring 5-phase - Ceiling-mounting bracket - White - - -

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information	
Number of light sources	3 [3 pcs]
Lamp family code	LED80S [LED Module, system flux 8000 lm]
Beam angle of light source	120 °
Light source colour	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	No [-]
Luminaire light beam spread	100° x 94°
Emergency lighting	No [-]
Control interface	-
Internal wiring	Standard
Feed-through wiring	Feed-through wiring 5-phase

Connection	CU5 [Connection unit 5-pole]
Cable	-
Protection class IEC	Safety class I (I)
Mounting	SMB [Ceiling-mounting bracket]
Ready-to-install	-
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
Accessories included	MB-SW [Mounting bracket for suspension wire]
CE mark	CE mark
ENEC mark	ENEC mark
Mechanical accessories	No [-]
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is

CoreLine Trunking

	no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	LL121X [CoreLine Trunking]
Unified glare rating CEN	Not applicable

Light Technical

Light distribution	DIR [Direct lighting]
--------------------	------------------------

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	No [-]
Circuit option	5 [5 conductors]
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.97

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	1730 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-

Colour	White
Dimensions (height x width x depth)	52 x 95 x 1730 mm (2 x 3.7 x 68.1 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	8000 lm
Luminous flux tolerance	+/-1%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	54 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

Product Data

Full product code	871869638094900
Order product name	LL121X LED80S/840 1x PSU WB 5 WH
EAN/UPC – product	8718696380949
Order code	38094900
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910925863973
SAP net weight (piece)	3.690 kg





CoreLine Trunking

Dimensional drawing

//

CoreLine electr. units LL120X-LL122X

Photometric data



IFGU1_LL121X1xLED80S840WB

IFPC1_LL121X1xLED80S840WB

