



CoreLine Recessed

RC134B LED37S/830 PSD W30L120 ELB3 NOC

Coreline Recessed - 830 warm white - Power supply unit with DALI interface

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Product data

General Information			
Light source colour	830 warm white	Glow-wire test	850/30 [Temperature 850 °C, duration 30 s]
Light source replaceable	No	Flammability mark	F [For mounting on normally flammable surfaces]
Number of gear units	1 unit	CE mark	CE mark
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	5 years
Optic type	WB [Wide beam]	Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median
Luminaire light beam spread	93°		
Control interface	DALI		
Connection	PIP [Push-in connector and pull relief]		
Cable	-		
Protection class IEC	Safety class I (I)		

CoreLine Recessed

	useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	24
EU RoHS compliant	Yes
Product family code	RC134B [Coreline Recessed]
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.275 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Textured
Overall length	1197 mm
Overall width	297 mm
Overall height	41 mm
Colour	White
Dimensions (height x width x depth)	41 x 297 x 1197 mm (1.6 x 11.7 x 47.1 in)

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	3700 lm
Luminous flux tolerance	+/-8%
Initial LED luminaire efficacy	95 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.43, 0.40) SDCM <3
Initial input power	39 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1% (no dimming in emergency mode)
Suitable for random switching	Yes

Product Data

Full product code	871869934842700
Order product name	RC134B LED37S/830 PSD W30L120 ELB3 NOC
EAN/UPC – product	8718699348427
Order code	34842700
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	910925864801
Net Weight (Piece)	3.750 kg



Dimensional drawing



CoreLine Recessed RC134B/RC135B

CoreLine Recessed

