



CoreLine Panel

RC132V G4 LED43S/840 PSD W60L60 OC

840 neutral white - Power supply unit with DALI interface

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Warranty period	
Beam angle of light source	- °	Warranty period	5 years
Light source colour	840 neutral white	Constant light output	No
Light source replaceable	No	Number of products on MCB (16 A type B)	30
Number of gear units	1 unit	EU RoHS compliant	Yes
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Unified glare rating CEN	19
Driver included	Yes	Light Technical	
Optic type	90 [Beam angle 90°]	Saturated Red	<50
Luminaire light beam spread	90°	Operating and Electrical	
Control interface	-	Input Voltage	220 to 240 V
Connection	Connection unit 2-pole	Input frequency	50 or 60 Hz
Cable	-	Initial CLO power consumption	- W
Protection class IEC	Safety class II (II)	Average CLO power consumption	- W
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]	Inrush current	14.3 A
Flammability mark	NO [-]	Inrush time	0.214 ms
CE mark	CE mark	Power factor (min.)	0.9
ENEC mark	ENEC mark		

CoreLine Panel

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover/lens material	Polystyrene
Fixation material	-
Optical cover/lens finish	Opal
Overall length	595 mm
Overall width	595 mm
Overall height	11 mm
Colour	White
Dimensions (height x width x depth)	11 x 595 x 595 mm (0.4 x 23.4 x 23.4 in)

Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]

Initial Performance (IEC Compliant)

Initial luminous flux	4300 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	125 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.39, 0.39) SDCM ≤3
Initial input power	34.5 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life	0.05 %
50,000 h	
Lumen maintenance at median useful life*	-
35,000 h	
Lumen maintenance at median useful life*	L80
50,000 h	
Lumen maintenance at median useful life*	-
75,000 h	
Lumen maintenance at median useful life*	-
100,000 h	

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	Not applicable

Product Data

Full product code	871016336047800
Order product name	RC132V G4 LED43S/840 PSD W60L60 OC
EAN/UPC – product	8710163360478
Order code	36047800
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	911401879180
SAP net weight (piece)	3.300 kg



Dimensional drawing



CoreLine Panel RC132V/RC133V

CoreLine Panel

