

# BT-ALU EM ballasts for TL Fluorescent lamps

## BT-ALU 18W 220V C 'SC



Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps; ideal solution for economical high-quality performance

### Product data

General Information		Temperature	
Application code	18W	T-winding (max.)	130 °C
Design	C	Delta-T normal conditions	65 °C
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 V	Housing	L 155x39x28
Input frequency	50 Hz	Approval and Application	
Power factor 100% load (min.)	0.85	Energy efficiency index	C
Input current with PF correction	0.12 A	Approval marks	CCC certificate
Input current without PF Correction	0.31 A	Product Data	
Power factor with PF compensation	0.35	Full product code	872790085753500
Power losses (nom.)	8.2 W	Order product name	BT-ALU 18W 220V C SC
Wiring		EAN/UPC – product	8711500998101
Connector type	Screw	Order code	85753500
System characteristics		SAP numerator – quantity per pack	1
Rated ballast-lamp power	18 W	Numerator – packs per outer box	32
		Material no. (12 NC)	913710124850
		SAP net weight (piece)	0.528 kg

## BT-ALU EM ballasts for TL Fluorescent lamps

### Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BT-ALU 18W	4.0	28.0	1.2	155.0	140.0	48.0	72.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

BT-ALU 18W 220V C 'SC

