



# Plusline Compact

## Plusline C 150W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light


### Product data

General Information	
Cap base	R7S [ R7s]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Light Technical	
Luminous flux (nom.)	2400 lm
Luminous efficacy (rated) (nom.)	16 lm/W
Colour rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	150 W
Lamp current (nom.)	0.65 A
Starting time (nom.)	0.0 s
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear

Cap-base information	10
Approval and Application	
Energy efficiency label (EEL)	D
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790080887200
Order product name	Plusline C 150W R7s 230V 1CT/10X10F
EAN/UPC – product	8727900808872
Order code	80887200
Numerator – quantity per pack	1
SAP numerator – packs per outer box	100
Material no. (12 NC)	923919943202
SAP net weight (piece)	0.005 kg
ILCOS code	HDG//RS-150-230-R7s-74,9

## Plusline Compact

### Dimensional drawing



#### Product

Plusline C 150W R7s 230V 1CT/10X10F

DEComp 150W R7s 230V T3 CL

