



# Appliance Oven Tubular

Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO

Tubular vacuum lamps with clear glass (T-bulb)

## Product data

General Information	
Cap base	E14 [ E14]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Oven
Nominal lifetime (nom.)	1000 h
Switching cycle	4.000X
Light Technical	
Luminous flux (nom.)	90 lm
Luminous flux (rated) (nom.)	90 lm
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	15.0 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Approval and Application	
Energy efficiency label (EEL)	E
Energy consumption kWh/1,000 hours	15 kWh
Product Data	
Full product code	871150003659905
Order product name	Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO
EAN/UPC – product	8711500036599
Order code	03659905
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	924196244442
SAP net weight (piece)	10.500 g
ILCOS code	IBT/C-15-230/240-E14-22*

## Appliance Oven Tubular

### Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230-240V T22CL OV 1CT/20F/NO	22 mm	49 mm



APP 15W E14 230-240V T22 CL OV

