



# Halogen Clickline G9

## Halogen MV Click 28W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.


### Product data

General Information	
Cap base	G9 [ G9]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Light Technical	
Luminous flux (nom.)	370 lm
Luminous flux (rated) (nom.)	370 lm
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	12.1 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	28.0 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Approval and Application	
Energy efficiency label (EEL)	D
Energy consumption kWh/1,000 hours	28 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790086398700
Order product name	Halogen MV Click 28W G9 230V CL 1CT
EAN/UPC – product	8727900863987
Order code	86398700
Numerator – quantity per pack	1
Numerator – packs per outer box	100
SAP material	925640644205
SAP net weight (piece)	0.003 kg

## Halogen Clickline G9

### Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

CLICKLINE 28W G9 230V CL

