



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Operating and Electrical	
Cap base	PGJX28 [ PGJX28]	Power (Rated) (Nom)	700 W
Operating position	UNIVERSAL [ Any or Universal (U)]	Lamp current (nom.)	10.2 A
Main application	Entertainment	Ignition supply voltage (min.)	198 V
Life to 50% failures (nom.)	750 h	Chromaticity coordinate X (nom.)	300
System description	MiniFastFit	Chromaticity coordinate Y (nom.)	324
Light Technical		Correlated Colour Temperature (Nom)	7200 K
Colour Code	2	Luminous efficacy (rated) (nom.)	69 lm/W
Luminous flux (min.)	44000 lm	Colour rendering index (nom.)	75
Luminous flux (nom.)	47000 lm		

# MSR Gold™ MiniFastFit (Touring/Stage)

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap-base information	PGJX28
----------------------	--------

## Luminaire Design Requirements


Bulb temperature (max.)	950 °C
Pinch temperature (max.)	500 °C

## Product Data

Full product code	871829122117300
-------------------	-----------------

Order product name	MSR Gold™ 700/2 MiniFastFit 1CT/4
EAN/UPC – product	8718291221173
Order code	22117300
Numerator – quantity per pack	1
SAP numerator – packs per outer box	4
Material no. (12 NC)	928199905115
Net Weight (Piece)	0.052 kg



## Dimensional drawing



MSR GOLD 700/2 MiniFastFit

Product	D (max)	O (max)	L (min)	L (max)	L (max)	C (max)	F (max)	F (max)	F (min)
MSR Gold™ 700/2 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

## Photometric data



XDPB\_XDMSR\_0004-Spectral power distribution B/W

## MSR Gold™ MiniFastFit (Touring/Stage)

