



CorePro LEDcandle

CorePro lustre ND 4-25W E14 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.


Product data

General Information		Warm-up time to 60% light (nom.)		0.5 s
Cap base	E14 [E14]	Power factor (nom.)	0.4	
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V	
Nominal lifetime (nom.)	15000 h	Temperature		
Switching cycle	50,000X	T-Case maximum (nom.)	75 °C	
Technical type	4-25W	Controls and Dimming		
Light Technical		Dimmable	No	
Colour Code	827 [CCT of 2,700 K]	Mechanical and Housing		
Luminous flux (nom.)	250 lm	Lamp Finish	Frosted	
Colour designation	Warm White (WW)	Approval and Application		
Correlated Colour Temperature (Nom)	2700 K	Energy efficiency label (EEL)	A+	
Luminous efficacy (rated) (nom.)	62.50 lm/W	Energy consumption kWh/1,000 hours	4 kWh	
Colour consistency	<6	Product Data		
Colour rendering index (nom.)	80	Full product code	871829178703700	
LLMF at end of nominal lifetime (nom.)	70 %	Order product name	CorePro lustre ND 4-25W E14 827 P45 FR	
Operating and Electrical		EAN/UPC – product	8718291787037	
Input frequency	50 to 60 Hz	Order code	78703700	
Power (Rated) (Nom)	4 W	SAP numerator – quantity per pack	1	
Lamp current (nom.)	35 mA			
Wattage equivalent	25 W			
Starting time (nom.)	0.5 s			

CorePro LEDcandle

Numerator – packs per outer box	10
SAP material	929001157502
SAP net weight (piece)	0.040 kg



Dimensional drawing



LED ND 4-25W E14 827 220-240V P45 FR


Product	D	C
CorePro lustre ND 4-25W E14 827 P45 FR	45 mm	88 mm

Photometric data



CorePro LEDlustre 4-25W E14 827 FR P45

CorePro LEDlustre 4-25W E14 827 FR P45




SDPO_LEDLSR_0003-Spectral Power distribution

CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

