

Classic filament LEDbulbs

CLA LEDBulb ND 4-40W ST64 E27 827 CL

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Starting time (nom.)	
Cap base	E27 [E27]		0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.4
Switching cycle	20,000X	Voltage (Nom)	220-240 V
Technical type	4-40W	Temperature	
Light Technical		T-Case maximum (nom.)	70 °C
Colour Code	827 [CCT of 2,700 K]	Controls and Dimming	
Luminous flux (nom.)	470 lm	Dimmable	No
Colour designation	Warm White (WW)	Mechanical and Housing	
Correlated Colour Temperature (Nom)	2700 K	Lamp Finish	Clear
Luminous efficacy (rated) (nom.)	118.00 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A++
Colour rendering index (nom.)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	No
Operating and Electrical		Energy consumption kWh/1,000 hours	4 kWh
Input frequency	50 to 60 Hz	Product Data	
Power (Rated) (Nom)	4 W	Full product code	871869657403400
Lamp current (nom.)	33 mA		
Wattage equivalent	40 W		

Classic filament LEDbulbs

Order product name	CLA LEDBulb ND 4-40W ST64 E27 827 CL
EAN/UPC – product	8718696574034
Order code	57403400
Numerator – quantity per pack	1
SAP numerator – packs per outer box	10

Material no. (12 NC)	929001237302
Net Weight (Piece)	0.030 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
CLA LEDBulb ND 4-40W ST64 E27 827 CL	64 mm	140 mm


Photometric data



LED Lamps, Lightcolour /827 ND CL



CorePro LEDbulb ND 4-40W ST64 827



CorePro LEDbulb ND 4-40W ST64 827

Classic filament LEDbulbs

