



# Essential LEDtube

## LEDtube HO 600mm 10W 740 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

### Product data

General Information		Voltage (Nom)	
Cap base	G13 [ Medium Bi-Pin Fluorescent]	220–240 V	
EU RoHS compliant	Yes	Temperature	
Nominal lifetime (nom.)	15000 h	T-ambient (max.)	45 °C
Switching cycle	50,000X	T-ambient (min.)	-20 °C
Light Technical		T storage (max.)	65 °C
Colour Code	740 [ CCT of 4,000 K]	T storage (min.)	-40 °C
Beam Angle (Nom)	240 °	T-Case maximum (nom.)	65 °C
Luminous flux (nom.)	1050 lm	Controls and Dimming	
Colour designation	Cool White (CW)	Dimmable	No
Correlated Colour Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	105.00 lm/W	Product length	600 mm
Colour consistency	<7	Approval and Application	
Color rendering index (nom.)	70	Energy efficiency label (EEL)	A+
LLMF at end of nominal lifetime (nom.)	70 %	Energy-saving product	Yes
Operating and Electrical		Approval marks	RoHS compliance KEMA Keur certificate
Input frequency	50 to 60 Hz	Energy consumption kWh/1,000 hours	10 kWh
Power (Rated) (Nom)	10 W	Product Data	
Starting time (nom.)	0.5 s	Full product code	871869667438300
Warm-up time to 60% light (nom.)	0.5 s		
Power factor (nom.)	0.5		

# Essential LEDtube

Order product name	LEDtube HO 600mm 10W 740 T8 AP I G
EAN/UPC – product	8718696674383
Order code	67438300
SAP numerator – quantity per pack	1
SAP numerator – packs per outer box	10

Material no. (12 NC)	929001277408
SAP net weight (piece)	0.120 kg



## Dimensional drawing

A3

Product	D1	D2	A1	A2	A3
LEDtube HO 600mm 10W 740 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


### TLED Ecofit APR HO 600mm 2ft T8 220-240V

## Photometric data



### LEDtube HO 10W G13 740 T8 AP I G


### LEDtube HO 20W G13 730 T8 AP I G




### LEDtube HO 10W G13 740 T8 AP I G

# Essential LEDtube


## Lifetime




LEDtube HO 20W G13 730 T8 AP I G




LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

## Essential LEDtube

