



Essential LED

ESS LED 9W E27 2700K 230V R80

Essential LED is an affordable LED spot lamp that is suitable for replacing halogen spot lamps. It provides a natural lighting effect as well as instant energy savings – an environmentally friendly solution. The Philips Essential LED family is designed for spot and general lighting applications in the hospitality, retail and home segments.

Product data


General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
Technical type	9-80W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Beam Angle (Nom)	120 °
Luminous flux (nom.)	880 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	97.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	0.7 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	9 W
Lamp current (nom.)	65 mA
Wattage equivalent	80 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	72 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	9 kWh
Product Data	
Full product code	871869679817100
Order product name	ESS LED 9W E27 2700K 230V R80
EAN/UPC – product	8718696798171
Order code	79817100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12

Essential LED

SAP material	929001857908
SAP net weight (piece)	0.040 kg



Dimensional drawing



R80 220-240V 8.5W 850lm 2700K E27 ND

Product	D	C
ESS LED 9W E27 2700K 230V R80	80 mm	115 mm


Photometric data



OSRAM Powerline LED Philips Lighting B.V. Page 11

LEDspot ESS 10W E27 R80 827 12D ND RCA



LEDspot ESS 10W E27 R80 827 12D ND RCA



LEDspot ESS 10W E27 R80 827 12D ND RCA

Essential LED

Lifetime



LEDspot ESS 4W E14 R50 827 12D ND RCA

LEDspot ESS 4W E14 R50 827 12D ND RCA

